




P	LTR	DESCRIPTION	DATE	DWN	APVD
A		RELEASE TO PRODUCTION	02APR2020	AY	PS
A1		SMART PN DETAILS ADDED	15FEB2022	SCB	PS




NOTES:

1. MATERIAL:
LCP BLACK, UL94 V0
2. N = NUMBER OF POSITION PER HOUSING.
3. HOUSING TO BE USED WITH CRIMP CONTACTS
2316113 (AWG 28-24/0.08-0.22 mm²) AND
2316114 (AWG 30-28/0.05-0.08 mm²)
4. PACKAGING : BULK BOX




CENTERLINE FOR ODD AND EVEN POSITION HOUSINGS

SCALE 5:1



DUAL ROW HOUSING
PLAIN VERSION
1- -0 AS SHOWN



SCALE 5:1

50.1	50	2MM-RC-D25-BX
48.1	48	2MM-RC-D24-BX
46.1	46	2MM-RC-D23-BX
44.1	44	2MM-RC-D22-BX
42.1	42	2MM-RC-D21-BX
40.1	40	2MM-RC-D20-BX
38.1	38	2MM-RC-D19-BX
36.1	36	2MM-RC-D18-BX
34.1	34	2MM-RC-D17-BX
32.1	32	2MM-RC-D16-BX
30.1	30	2MM-RC-D15-BX
28.1	28	2MM-RC-D14-BX
26.1	26	2MM-RC-D13-BX
24.1	24	2MM-RC-D12-BX
22.1	22	2MM-RC-D11-BX
20.1	20	2MM-RC-D10-BX
18.1	18	2MM-RC-D09-BX
16.1	16	2MM-RC-D08-BX
14.1	14	2MM-RC-D07-BX
12.1	12	2MM-RC-D06-BX
10.1	10	2MM-RC-D05-BX
8.1	8	2MM-RC-D04-BX
6.1	6	2MM-RC-D03-BX
4.1	4	2MM-RC-D02-BX
DIM "E"	N	SMART PN

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.15 2 PLC ±0.10 3 PLC ± 4 PLC ± ANGLES ±2° FINISH -	DWN 29OCT2017 RAKSHITH R NAYAK CHK 29OCT2017 RAKSHITH R NAYAK APVD 11DEC2017 PRASHANTH S	NAME AMPMODU 2mm RECEPTACLE, w/B HOUSING, CRIMP, DUAL ROW, PLAIN
MATERIAL SEE NOTE 1		PRODUCT SPEC 108-64040-1	SIZE A2
		APPLICATION SPEC 114-32173	CAGE CODE 00779
		WEIGHT -	DRAWING NO C-2316108
		CUSTOMER DRAWING	RESTRICTED TO -

SCALE 10:1 SHEET 1 OF 2 REV A1

P	LTR	DESCRIPTION	DATE	DWN	APVD
-		SEE SHEET 1	-	-	-

SMART PART NUMBER
2MM -RC - D__ - BX

PRODUCT SERIES

2MM AMPMODU 2mm SERIES

GENDER / TYPE

RC RECEPTACLE HOUSING FOR CRIMP TYPE (STANDARD)

NUMBER OF ROWS

D DUAL ROW

PACKAGING


BX BOX

NUMBER OF PINS PER ROW

XX 02 THROUGH 25
(ENTER TWO DIGITS)

SMART PN EXAMPLES:

- 2MM-RC-D02-BX:
AMPMODU 2mm, RECEPTACLE HOUSING FOR CRIMP TYPE (STANDARD), DUAL ROW, 02 POSITION PER ROW, BOX PACKAGING
- 2MM-RC-D25-BX:
AMPMODU 2mm, RECEPTACLE HOUSING FOR CRIMP TYPE (STANDARD), DUAL ROW, 25 POSITION PER ROW, BOX PACKAGING

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 29OCT2017 RAKSHITH R NAYAK	 TE Connectivity	
DIMENSIONS: mm		CHK 29OCT2017 RAKSHITH R NAYAK		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 11DEC2017 PRASHANTH S	NAME AMPMODU 2mm RECEPTACLE, w/B HOUSING, CRIMP, DUAL ROW, PLAIN	
0 PLC ±		PRODUCT SPEC	RESTRICTED TO	
1 PLC ±0.15		108-64040-1	-	
2 PLC ±0.10		APPLICATION SPEC	SIZE	CAGE CODE
3 PLC ±		114-32173	A2	00779
4 PLC ±		WEIGHT	DRAWING NO	
ANGLES ±2°		-	C-2316108	
FINISH		SCALE		SHEET
SEE NOTE 1		1:1		2 OF 2
-		CUSTOMER DRAWING		REV A1