



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	30NOV2018	HC	YJ
	AI	REVISED(ECR-19-008548)	03JUN2019	EW	YJ
	B	REVISED(ECR-19-017790)	17MAR2020	HC	YJ
	C	REVISED(ECR-21-106238)	01FEB2021	HC	YJ




SCALE 1:1

LEVER OPEN POSITION



3D ISO VIEW
SCALE 1:1



<DELIVERY CONDITION>

NOTES:

1. GENERAL TOLERANCE : ± 0.5

2. APPLICABLE CONNECTOR : 2321359-1, 2321359-2, 2321359-4, 2321359-5
1-2321359-1, 1-2321359-2, 1-2321359-7, 1-2321359-6



 MAX 85 PIN(WIRE) CAN BE USED ON THIS PACKAGE
 (2-2321366-2, 3-2321366-2)


 IF USE TERMINAL MORE THAN 85PIN BY REDUCING EACH SQ SIZE,
 SHOULD BE CHECKED FOR WORK-ABILITY, ASSEMBLY-ABILITY
 IN LAY-OUT BEFORE USE.

FOLLOW THE TABLE FOR THE ALLOWED MAX PIN NUMBER AND POISION

TERMINAL	050 TERMINAL	050 TERMINAL	110 TERMINAL
MAX SQ	MAX 0.75SQ	MAX 1.25SQ	MAX 2.5SQ
CURCIT NO (CONNECTOR)	5~24 28~47 51~70 74~93 97~116	25~27 48~50 71~73 94~96 117~119	1~4
ALLOWED MAX PIN (CONNECTOR MAX)	66 (100)	15 (15)	4 (4)


4-2321366-2 : CONNECTOR ENGAGE/DISENGAGE FORCE IS TESTED
BY NX4 ACTUAL PIN MAP, NOT FULL PIN
AVAILABLE MAX PIN(050 TERMIAL : 73 / 110 TEERMINAL : 4)

C	B	8	BLACK	PA6-GF33	LEVER (VERTICAL CN7a)	I	-	-	-	-	-
	B	7	BLACK	PA6-GF33	LEVER (VERTICAL NX4)	-	I	-	-	-	-
A1	B	6	BLACK	PA6-GF33	LEVER (VERTICAL)	-	-	I	I	I	-
		5	BLACK	PA66-GF30	LEVER (BASIC)	-	-	-	-	-	I
C	B	4	BLACK	PA6-GF33	COVER HOUSING (CENTER RH)	-	-	I	-	-	-
	B	3	BLACK	PA6-GF33	COVER HOUSING (CENTER LH)	I	-	-	I	-	-
A1	B	2	BLACK	PA6-GF33	COVER HOUSING (VERTICAL)	-	I	-	-	I	-
		1	BLACK	PA66-GF30	COVER HOUSING (BASIC)	-	-	-	-	-	I
		NO	COLOR/FINISH	MATERIAL	DESCRIPTION	QT'Y	QT'Y	QT'Y	QT'Y	QT'Y	QT'Y

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN EW CHUN		TE Connectivity							
		CHK YD. LEE									
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED.		NAME							
		APVD YJ YOUN		050/110 119P COVER ASSY							
		PRODUCT SPEC									
		APPLICATION SPEC		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
MATERIAL		WEIGHT		A2		00779		C=2321366		-	
FINISH		CUSTOMER DRAWING		SCALE		2:1		SHEET		1 of 3	
SEE TABLE										REV C	

printed on 20 Jul 2021 17:07 (1) from FC001932

1471-9 (3/13)



B

3

4

C

119P ECU COVER ASSY(CENTER LH)
2-2321366-2

SCALE 1:1

B

3

4

C


6

119P ECU COVER ASSY (CENTER LH CN7a)
5-2321366-2

SCALE 1:1

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			



(41.8)

(76.76)

6

3

73.6±0.5

80.4±0.5

(116.94)

(34.4)

<DELIVERY CONDITION>

SCALE 1:2

C

(41.8)

(76.76)

8

3

73.6±0.5

80.4±0.5

(106.94)

(34.4)

