











REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASE	26JUL17	K.W	I.Y
	A1	ECR-20-011383	02SEP20	K.W	W.W
	A2	ECN-21-129967	02DEC21	T.T	J.Z



ISOMETRIC VIEW
SCALE 2:1



- 1 PLASTIC MATERIAL: PA10T OR SPS
SQ PIN MATERIAL: CuZn30
PLATING SPEC: TIN OVER NICKEL
- 2 MATERIAL MARKING
- 3 PLASTIC HOUSING PRODUCTION MONTH CLOCK
- 4 TOOL CAVITY MARKING 1.2.3.4...
5. PRODUCT OPERATION TEMPERATURE RANGE:-40°C~105°C
6. SUITABLE MATING CONNECTOR: 2322637
- 7 TE-LOGO
- 8 TE SEMIFINISHED PART NUMBER
- 9 TE SEMIFINISHED PART REVISION
- 10 PRODUCT STABILIZATION FOR SOLDERING PROCESS
- 11 PRODUCT ASSEMBLY DATA INFORMATION



SCALE 2:1
ISOMETRIC VIEW

2-2322610-1	A-D	REEL(D IM:380*380*44mm)	6	0.63 SQ PIN	CuZn30	Sn OVER Ni	3
			6	0.63 SQ PIN	CuZn30	Sn OVER Ni	2
			1	12 WAY HOUSING	PA10T OR SPS	BLACK	1
1-2322610-1	A-D	TRAY(D IM:320*210*28mm)	6	0.63 SQ PIN	CuZn30	Sn OVER Ni	3
			6	0.63 SQ PIN	CuZn30	Sn OVER Ni	2
			1	12 WAY HOUSING	PA10T OR SPS	BLACK	1
2322610-4	B-D	TRAY(D IM:375*275*30mm)	6	0.63 SQ PIN	CuZn30	Sn OVER Ni	3
			6	0.63 SQ PIN	CuZn30	Sn OVER Ni	2
			1	12 WAY HOUSING	PA10T OR SPS	BLUE	1
2322610-3	A-C	TRAY(D IM:375*275*30mm)	6	0.63 SQ PIN	CuZn30	Sn OVER Ni	3
			6	0.63 SQ PIN	CuZn30	Sn OVER Ni	2
			1	12 WAY HOUSING	PA10T OR SPS	GREEN	1
2322610-2	B-C	TRAY(D IM:375*275*30mm)	6	0.63 SQ PIN	CuZn30	Sn OVER Ni	3
			6	0.63 SQ PIN	CuZn30	Sn OVER Ni	2
			1	12 WAY HOUSING	PA10T OR SPS	BROWN	1
2322610-1	A-D	TRAY(D IM:375*275*30mm)	6	0.63 SQ PIN	CuZn30	Sn OVER Ni	3
			6	0.63 SQ PIN	CuZn30	Sn OVER Ni	2
			1	12 WAY HOUSING	PA10T OR SPS	BLACK	1
TE P/N	CODING	PACKAGE TYPE	QTY	DESCRIPTION	MATERIAL	COLOR/FINISH	ITEM NO
			PART LIST				

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K.WEI CHK E. JIANG		12JUL2017 21JUL2017		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD LYIN		NAME 12 WAY MQS PIN HEADER	
		0 PLG ± 1 PLG ±0.1 2 PLG ±0.01 3 PLG ±0.004 4 PLG ±0.0001 ANGLES ±		PRODUCT SPEC 108-101528		SIZE	
MATERIAL		FINISH		APPLICATION SPEC 114-101065		CAGE CODE	
		-		WEIGHT -		DRAWING NO	
				A2		-	
				CUSTOMER DRAWING		C=2322610	
						RESTRICTED TO	
						SCALE 2:1	
						SHEET 1 OF 1	
						REV A2	

