




REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	03OCT2018	STK	DM
	A1	REVISED PER PCN E-19-002027	07MAR2019	SS	DM



3 MATERIAL: HOUSING/CAP: PA66 GF15 (GRAY OR BLACK).
 GROMMET: VMQ (RED-ORANGE).
 WEDGE LOCK: PBT GF30 (GREEN).
 CONTACTS: COPPER ALLOY, GOLD PLATED.

- 2. RESISTOR IS INSERTED INTO CAVITIES 1 AND 2
 RESISTOR CHARACTERISTICS: $\Omega \pm 1\%$, 0.25WATTS.
- 1. THIS RECEPTACLE MATES WITH DT06-2S-XXXX PLUG.
 (XXXX = ALL MODIFICATIONS)

NOTES: UNLESS OTHERWISE SPECIFIED

BLACK	100K	1-2322907-1	DT04-2P-TR32-100K
GRAY	4700	1-2322907-2	DT04-2P-TR31-4700
GRAY	750	2-2322907-2	DT04-2P-TR31-750
COLOR	RESISTANCE (Ω)	TE PN	DEUTSCH PN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. TEJUS KIRAN 26 JUL 2018					
DIMENSIONS: INCHES [mm]		CHK KASHYAP P B 03OCT2018					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD DAVID MEYER 03OCT2018	NAME 2 WAY RECEPTACLE TERMINATING RESISTOR DT SERIES				
0 PLC \pm - 1 PLC \pm - 2 PLC \pm - 3 PLC $\pm 0.025 [0.64]$ 4 PLC \pm - ANGLES $\pm 30' 0''$		PRODUCT SPEC 108-151009	SIZE A3	CAGE CODE 00779	DRAWING NO G-2322907	RESTRICTED TO -	
MATERIAL 3	FINISH	APPLICATION SPEC 0425-017-0000	WEIGHT 6.0 GR	SCALE 3:1		SHEET 1 OF 1	REV A1
CUSTOMER DRAWING							