




P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASE	04NOV2020	T.S	E.I

Δ MATERIAL AND FINISH
 HOUSING : LIQUID CRYSTAL PLASTIC, BLACK
 CONTACT : COPPER ALLOY, PLATING: CONTACT AREA SEE TABLE
 SOLDERING AREA TIN
 2. INSTRUCTION SHEET: 408-78171




CONTACT AREA D	DIM C	DIM B	DIM A	NO OF POSN	PART NUMBER	
0.38um GOLD	3	22.9	15	24.9	4	2-2336491-4
0.38um GOLD	2	17.9	10	19.9	3	2-2336491-3
TIN	3	22.9	15	24.9	4	2336491-4
TIN	2	17.9	10	19.9	3	2336491-3

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN H. OSABE 04NOV2020		NAME HEADER ASSEMBLY, 270 DEGREE TYPE D2970 PUSH-IN TYPE, DYNAMIC FIELD INSTALLABLE CONNECTOR	
CHK T. SHIMOYASU 04NOV2020			
APVD F. IKEMATSU 04NOV2020			
PRODUCT SPEC 108-140223			
MATERIAL	FINISH	APPLICATION SPEC -	
WEIGHT -	SCALE 3:1	SHEET 1 OF 2	RESTRICTED TO -
CUSTOMER DRAWING		REV A	

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±0.5
	1 PLC ±0.5
	2 PLC ±0.5
	3 PLC ±
	4 PLC ±
	ANGLES ±5°

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



RECOMMENDED PCB LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H. OSABE 15MAY2019		
DIMENSIONS: mm		CHK T. SHIMOYASU 15MAY2019		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD F. IKEMATSU 15MAY2019	NAME HEADER ASSEMBLY, 270 DEGREE TYPE D2970 PUSH-IN TYPE, DYNAMIC FIELD INSTALLABLE CONNECTOR	
0 PLC ±0.5 1 PLC ±0.5 2 PLC ±0.5 3 PLC ± 4 PLC ± ANGLES ±5°		PRODUCT SPEC 108-140223	RESTRICTED TO	
MATERIAL		APPLICATION SPEC	SIZE A3	CAGE CODE 00779
FINISH		WEIGHT	DRAWING NO C-2336491	SCALE 3:1
		CUSTOMER DRAWING	SHEET 2	OF 2
			REV A	