





REVISIONS				
P	LTN	DESCRIPTION	DATE	OWN APVD
A3		REVISED (ECO-21-001090)	26JAN2021	A.H I.Y
A4		REVISED (ECO-21-003425)	17MAR2021	A.H I.Y
A5		REVISED (ECN-22-154776)	19MAY2022	G.Y F.P
A6		REVISED (ECN-22-180983)	24OCT2022	G.Y F.P



- INTERFACE DESIGN ARE ACCORDING TO TE DRAWING: 208-18037 OR 208-18192
- CENTER OF GRAVITY
- ALL DIMENSIONS IN () FOR INFORMATION ONLY
- SOLDERING PROCESS: LEAD FREE REFLOW SOLDERING IN REFERENCE TO JEDEC J-STD-020D
- VACUM GRIP AREA FREE OF SCRATCH
- PCB TOP LAYER MUST BE GND PLANE, EXCEPT THE NEED SIGNAL PATHS AND CUT OUT AREA
- MATED WITH TE PLUG X-2333538-X OR X-2334013-X OR X-2317303-X.
- CUT OUT AREA IS VARIANT FOR CODINGS. DETAIL REFER TO CVM OR CONTACT WITH TE PRODUCT ENGINEER.
- TRAY SIZE:350*260*36.7mm.
- TRAY SIZE:320*210*29mm.
- PRODUCTION VALIDATION TEST ACCORDING TO LV214 (MBN10384) AND USCAR-2

PN FOR PACKAGE IN TUBE	PN FOR PACKAGE IN TRAY	REV.	CODE	QTY.	DESCRIPTION	MATERIAL	WEIGHT (g)	COLOR/SURFACE	POS
7-2339800-9	6-2339800-9	A	Z	12	PIN	Cu ALLOY	13.58	Ni/Sn	4
				1	HORIZONTAL SHIELD	Cu ALLOY		PRE-TIN	3
				4	VERTICAL SHIELD	STAINLESS STEEL		Ni/Sn	2
				1	HOUSING	PA10T-GF30		WATER BLUE	1
7-2339800-7	6-2339800-7	A	J	12	PIN	Cu ALLOY	13.58	Ni/Sn	4
				1	HORIZONTAL SHIELD	Cu ALLOY		PRE-TIN	3
				4	VERTICAL SHIELD	STAINLESS STEEL		Ni/Sn	2
				1	HOUSING	PA10T-GF30		BEIGE	1
7-2339800-3	6-2339800-3	A	C	12	PIN	Cu ALLOY	13.58	Ni/Sn	4
				1	HORIZONTAL SHIELD	Cu ALLOY		PRE-TIN	3
				4	VERTICAL SHIELD	STAINLESS STEEL		Ni/Sn	2
				1	HOUSING	PA10T-GF30		BLUE	1
7-2339800-2	6-2339800-2	A	B	12	PIN	Cu ALLOY	13.58	Ni/Sn	4
				1	HORIZONTAL SHIELD	Cu ALLOY		PRE-TIN	3
				4	VERTICAL SHIELD	STAINLESS STEEL		Ni/Sn	2
				1	HOUSING	PA10T-GF30		WHITE	1
7-2339800-1	6-2339800-1	A	A	12	PIN	Cu ALLOY	13.58	Ni/Sn	4
				1	HORIZONTAL SHIELD	Cu ALLOY		PRE-TIN	3
				4	VERTICAL SHIELD	STAINLESS STEEL		Ni/Sn	2
				1	HOUSING	PA10T-GF30		BLACK	1
4-2339800-9	4-2339800-9	A	Z	12	PIN	Cu ALLOY	13.96	Ni/Sn	4
				1	HORIZONTAL SHIELD	Cu ALLOY		PRE-TIN	3
				4	VERTICAL SHIELD	STAINLESS STEEL		Ni/Sn	2
				1	HOUSING	PA4T-GF30		WATER BLUE	1
4-2339800-7	4-2339800-7	A	J	12	PIN	Cu ALLOY	13.96	Ni/Sn	4
				1	HORIZONTAL SHIELD	Cu ALLOY		PRE-TIN	3
				4	VERTICAL SHIELD	Cu ALLOY		PRE-TIN	2
				1	HOUSING	PA4T-GF30		BEIGE	1
4-2339800-3	4-2339800-3	A	C	12	PIN	Cu ALLOY	13.96	Ni/Sn	4
				1	HORIZONTAL SHIELD	Cu ALLOY		PRE-TIN	3
				4	VERTICAL SHIELD	Cu ALLOY		PRE-TIN	2
				1	HOUSING	PA4T-GF30		BLUE	1
4-2339800-2	4-2339800-2	A	B	12	PIN	Cu ALLOY	13.96	Ni/Sn	4
				1	HORIZONTAL SHIELD	Cu ALLOY		PRE-TIN	3
				4	VERTICAL SHIELD	Cu ALLOY		PRE-TIN	2
				1	HOUSING	PA4T-GF30		WHITE	1
4-2339800-1	4-2339800-1	A	A	12	PIN	Cu ALLOY	13.96	Ni/Sn	4
				1	HORIZONTAL SHIELD	Cu ALLOY		PRE-TIN	3
				4	VERTICAL SHIELD	Cu ALLOY		PRE-TIN	2
				1	HOUSING	PA4T-GF30		BLACK	1
3-2339800-9	2-2339800-9	A	Z	12	PIN	Cu ALLOY	13.96	Ni/Sn	4
				1	HORIZONTAL SHIELD	Cu ALLOY		PRE-TIN	3
				4	VERTICAL SHIELD	STAINLESS STEEL		Ni/Sn	2
				1	HOUSING	PA4T-GF30		WATER BLUE	1
3-2339800-7	2-2339800-7	A	J	12	PIN	Cu ALLOY	13.96	Ni/Sn	4
				1	HORIZONTAL SHIELD	Cu ALLOY		PRE-TIN	3
				4	VERTICAL SHIELD	STAINLESS STEEL		Ni/Sn	2
				1	HOUSING	PA4T-GF30		BEIGE	1
3-2339800-3	2-2339800-3	A	C	12	PIN	Cu ALLOY	13.96	Ni/Sn	4
				1	HORIZONTAL SHIELD	Cu ALLOY		PRE-TIN	3
				4	VERTICAL SHIELD	STAINLESS STEEL		Ni/Sn	2
				1	HOUSING	PA4T-GF30		BLUE	1
3-2339800-2	2-2339800-2	A	B	12	PIN	Cu ALLOY	13.96	Ni/Sn	4
				1	HORIZONTAL SHIELD	Cu ALLOY		PRE-TIN	3
				4	VERTICAL SHIELD	STAINLESS STEEL		Ni/Sn	2
				1	HOUSING	PA4T-GF30		WHITE	1
3-2339800-1	2-2339800-1	A	A	12	PIN	Cu ALLOY	13.96	Ni/Sn	4
				1	HORIZONTAL SHIELD	Cu ALLOY		PRE-TIN	3
				4	VERTICAL SHIELD	STAINLESS STEEL		Ni/Sn	2
				1	HOUSING	PA4T-GF30		BLACK	1
1-2339800-9	2339800-9	A	Z	12	PIN	Cu ALLOY	13.96	Ni/Sn	4
				1	HORIZONTAL SHIELD	Cu ALLOY		PRE-TIN	3
				4	VERTICAL SHIELD	Cu ALLOY		PRE-TIN	2
				1	HOUSING	PA4T-GF30		WATER BLUE	1
1-2339800-7	2339800-7	A	J	12	PIN	Cu ALLOY	13.96	Ni/Sn	4
				1	HORIZONTAL SHIELD	Cu ALLOY		PRE-TIN	3
				4	VERTICAL SHIELD	Cu ALLOY		PRE-TIN	2
				1	HOUSING	PA4T-GF30		BEIGE	1
1-2339800-3	2339800-3	A	C	12	PIN	Cu ALLOY	13.96	Ni/Sn	4
				1	HORIZONTAL SHIELD	Cu ALLOY		PRE-TIN	3
				4	VERTICAL SHIELD	Cu ALLOY		PRE-TIN	2
				1	HOUSING	PA4T-GF30		BLUE	1
1-2339800-2	2339800-2	A	B	12	PIN	Cu ALLOY	13.96	Ni/Sn	4
				1	HORIZONTAL SHIELD	Cu ALLOY		PRE-TIN	3
				4	VERTICAL SHIELD	Cu ALLOY		PRE-TIN	2
				1	HOUSING	PA4T-GF30		WHITE	1
1-2339800-1	2339800-1	A	A	12	PIN	Cu ALLOY	13.96	Ni/Sn	4
				1	HORIZONTAL SHIELD	Cu ALLOY		PRE-TIN	3
				4	VERTICAL SHIELD	Cu ALLOY		PRE-TIN	2
				1	HOUSING	PA4T-GF30		BLACK	1

THIS DRAWING IS A CONTROLLED DOCUMENT. DWN: G.Y.CHEN 24OCT22
 CHK: D.ZHU 24OCT22
 APVD: F.PAN 24OCT22
 NAME: MATEnet 90deg HEADER 2X3 PORTS

TE Connectivity

SIZE: A1 CAGE CODE: DRAWING NO: 108-94568
 WEIGHT: see table
 RESTRICTED CUSTOMER

SCALE: 3:1 SHEET: 1 OF 1 REV: A6