

		TOLERANZ EN ISO 8015 TOLERIERUNG EN ISO 8015		2344956-1	PBT-GF10 FR	BLACK	COVER Abdeckkappe	A	1
DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT. BEMASSUNGEN UND TOLERANZEN GEMAESS GPS (ISO STANDARDS).				TE PART-NO. TE Teile-Nr.	MAT.	COLOUR Farbe	DESCRIPTION Beschreibung	REV.	ITEM
THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS).				DWN M. Floesser CHK P. Wrobel APVD F. Eltrop 02MAY2019 03MAY2019 03MAY2019  TE Connectivity					
DIMENSIONS: MASSE/WEITEN (mm)		TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN		NAME		COVER Abdeckkappe			
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ±		PRODUCT SPEC PRODUKTSPEZ.		-			
MATERIAL		ANGLES/WINKEL ± FINISH/OBERFLÄCHE/FARBE		APPLICATION SPEC VERARBEITUNGSSPEZ.		-			
-		-		WEIGHT GEWICHT		18.1g		-	
-		-		SIZE		CAGE CODE		DRAWING NO ZEICHNUNGS-NR.	
-		-		A2		00779		C=2344956	
CUSTOMER DRAWING				KUNDENZEICHNUNG		SCALE MASSSTAB		RESTRICTED TO NUR FÜR	
						2:1		SHEET BLATT	
						1 OF VON 1		REV A1	