

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	CREATION	19-DEC-18	GL	—

D

C

B

A



D

C

B

A


M10 Bolts stainless steel A4: 37Nm
Boulons M10 acier inoxydable A4: 37Nm



ø30.6-32.5


M10 stainless steel U-Bolt A4: 37Nm
Etrier M10 acier inoxydable A4: 37Nm

M10 Bolts stainless steel A4: 37Nm
Boulons M10 acier inoxydable A4: 37Nm



No scale — sans echelle

ITEM:.....

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN LAFORGE	19-DEC-18	 TE Connectivity					
		CHK —	—	NAME TEE CONNECTOR RACCORD EN TE 5 CT 82 MR325 MR345					
		APVD —	—						
		PRODUCT SPEC 108-69096-001							
		APPLICATION SPEC —							
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
		0 PLC	± —	APPROX.WEIGHT 2.3 kg	A300779	C=2349457	—		
		1 PLC	± —						
		2 PLC	± —						
		3 PLC	± —						
		4 PLC	± —						
MATERIAL		ANGLES	± —	CUSTOMER DRAWING					
		FINISH	—	SCALE	1:2	SHEET	1 OF 1	REV	A