



RETAINER PLATE
MATERIAL: ALUMINUM
FINIH: CHROMATE CONVERSION

CAPTIVE SCREWS
MATERIAL: STAINLESS STEEL
FINISH: PASSIVATED
QTY 2




SHELL BODY
MATERIAL: ALUMINUM
FINISH: CHROMATE CONVERSION

4 POSITION MT FIBER INSERT
MATERIAL: NICKEL SILVER COPPER
INSERT RETAINING RING
MATERIAL: STAINLESS STEEL
FINISH: PASSIVATED
INTERFACIAL SEAL
MATERIAL: RUBBER
COLOR: RED




FIBER OPTIC MT FERRULE CABLE ASSEMBLY
SHOWN FOR REFERENCE ONLY
FIBER OPTIC CABLE ASSEMBLIES
CAN BE ORDERED SEPARATELY




45 DEGREE
INSERT OPTION

- 1 FINISH: OLIVE DRAB, CADMIUM.
2 FINISH: NICKEL, ELECTROLESS
3 FINISH: NICKEL PTFE
4 FINISH: BLACK ZINC

5.8 MAX
PANEL THICKNESS



RECOMMENDED PANEL CUT-OUT



KEYING ORIENTATION DETAIL

KEYING ORIENTATION	A	B	C	D
N	95°	141°	208°	236°
A	113°	156°	182°	292°
B	90°	145°	195°	252°

2-2358897-4	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY B, BLACK ZINC, 45° INSERT	4
2-2358897-3	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY B, BLACK ZINC	4
2-2358897-2	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY A, BLACK ZINC, 45° INSERT	4
2-2358897-1	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY A, BLACK ZINC	4
2-2358897-0	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY N, BLACK ZINC, 45° INSERT	4
1-2358897-9	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY N, BLACK ZINC	4
1-2358897-8	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY B, NICKEL PTFE, 45° INSERT	3
1-2358897-7	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY B, NICKEL PTFE	3
1-2358897-6	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY A, NICKEL PTFE, 45° INSERT	3
1-2358897-5	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY A, NICKEL PTFE	3
1-2358897-4	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY N, NICKEL PTFE, 45° INSERT	3
1-2358897-3	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY N, NICKEL PTFE	3
1-2358897-2	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY B, NICKEL, 45° INSERT	2
1-2358897-1	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY B, NICKEL	2
1-2358897-0	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY B, OLIVE DRAB, 45° INSERT	1
2358897-9	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY B, OLIVE DRAB	1
2358897-8	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY A, NICKEL, 45° INSERT	2
2358897-7	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY A, NICKEL	2
2358897-6	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY A, OLIVE DRAB, 45° INSERT	1
2358897-5	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY A, OLIVE DRAB	1
2358897-4	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY N, NICKEL, 45° INSERT	2
2358897-3	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY N, NICKEL	2
2358897-2	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY N, OLIVE DRAB, 45° INSERT	1
2358897-1	RECEPTACLE CONNECTOR ASSEMBLY, SIZE 15, KEY N, OLIVE DRAB	1

ASSEMBLY PART NUMBER	DESCRIPTION
----------------------	-------------

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. FABIAN	16JUL2019
DIMENSIONS:		CM*	-
mm		APVD	-
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	-
0 PLC ±		APPLICATION SPEC	-
1 PLC ±		SIZE	CAGE CODE DRAWING NO
2 PLC ±0.13		WEIGHT	-
3 PLC ±0.013		CUSTOMER DRAWING	SCALE 2:1 SHEET 1 OF 1 REV B
4 PLC ±			
ANGLES ±1			
FINISH			



TE Connectivity

KIT, RECEPTACLE CONNECTOR ASSEMBLY
FIBER OPTIC, MT, SIZE 15, 4 CAVITY
38999 STYLE, FLANGE MOUNT

00779 ©=2358897