






PART NUMBER: 2359659-1								
CONTACT LAYOUT								
A: DIM A=4.5								
B: DIM A=4.9								
C: DIM A=5.5								
COLUMNS								
	1	2	3	4	5	6	7	8
A	C	C	C	C	C	C	C	A
B	C	C	C	C	C	C	C	C
C	C	C	C	C	C	C	C	C
D	C	C	C	C	C	C	C	C
E	C	C	C	C	C	C	C	C
F	C	C	C	C	C	C	C	C
G	C	C	C	C	C	C	C	C
H	C	C	C	C	C	C	C	C
J	A	C	C	C	C	C	C	C

- MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±0.25
2 PLC	±0.13
3 PLC	±
4 PLC	±
ANGLES	±
FINISH	SEE TABLE

MATERIAL

SEE TABLE

DWN: ALEX SHOAL 15JUL2019

CHK: SANDERS YAN 15JUL2019

APVD: HOPE LU 15JUL2019

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

NAME: IMPACT, 3 PAIR, 8 COLUMN, HEADER UNGUIDED, RIGHT END WALL SIGNAL MODULE, 0.46 PTH

SIZE: A | 00779 | C=2359659

SCALE: 6:1

SHEET: 1 OF 1

REV: A

TE Connectivity