



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW RELEASE	24FEB2022	SSH	KPB
	A2	PCN-23-183884	10AUG2023	RN	KPB



AS SHOWN
2402050-1
SCALE 1:1





NOTES

1 HANDLING OF PARTS ONLY WITH GLOVES.

A2 2 PLATING THICKNESS ON CONTACT AREA min. 0.5µm Cu AS PER 112-300-2, 8.5-13µm Ag AS PER 112-32-2 PASSIVATION AS PER 118-91.

AS SHOWN
2402050-1
SCALE 1:2



A2 2	1	1-2342880-1	A	8MM PIN WITH PROTECTION CAP	MIXED	MIXED	2
	1	2390837-5	A	BUSBAR, WELD PAD, STRAIGHT	Cu-OF R215 TEC-100-316	BLANK	1
	2402050-1	PART NO	REV	DESCRIPTION	MATERIAL	SURFACE/ COLOR	ITEM NO
A	REVISION OF EACH ASSY NO (WHEN BLANK, USE DWG REVISION)						
CONTACT ASSY	PARTS LIST						

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS).

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±
	1 PLC ±0.1
	2 PLC ±0.01
	3 PLC ±0.001
	4 PLC ±0.0001
	ANGLES ±
MATERIAL	FINISH
-	-
-	-

DWN	23FEB2022
SUBHAS H	
CHK	23FEB2022
AMRUTHA R C H	
APVD	23FEB2022
KASHYAP P B	
PRODUCT SPEC	108-94867 A2
APPLICATION SPEC	114-94758 A2
WEIGHT	-
CUSTOMER DRAWING	

TE Connectivity			
NAME PIN, DIA8.0 CONTACT ASSY			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2402050	-
SCALE	SHEET	OF	REV
1:1	1	1	A2

DIMENSION AND TOLERANCES ACCORDING TO:
Bemaßungen und Toleranzen gemäß:

DIN 16742
DIN EN ISO 8015 (AD) - DIN EN ISO 291
DIN EN ISO 14405-1/-2/-3