





P	LTR	DESCRIPTION	DATE	DWN	APVD
	1	NEW RELEASE	29SEP2023	MM	MM
	2	CORRECT NOTES	17OCT2023	MM	MM
	A	ECN-23-236574	25OCT2023	RK	MM

ELECTRICAL CHARACTERISTICS:	
SUPPLY VOLTAGE	24Vdc ± 10%
PEAK POWER CONSUMPTION	0.5W MAXIMUM
AVERAGE POWER CONSUMPTION	0.3W
OPERATING LIGHT LEVELS	35 LUX ON, 18 LUX OFF ±7.5%
TIME DELAY ON/OFF	25 SECONDS
STANDARDS COMPLIANCE	UL-773 ZHAGA D4i (DALI-2) TYPE A DEVICE
TIME REFERENCE STABILIZATION	3 DAYS MAXIMUM
TIME ACCURACY	± 15 MINUTES
DIMMING SCHEDULE	100% - DUSK (35 LUX) TO 00:00 (MIDNIGHT) 50% - 00:00 - 05:30 100% - 5:30 - DAWN (18 LUX)
ENVIRONMENTAL CHARACTERISTICS:	
OPERATING TEMPERATURE	-40 TO 80°C
SEALING/IMPACT	IP-66 / IK-09
RELATIVE HUMIDITY	0 TO 90%,NON-CONDENSING ENVIRONMENT



NOTES:

- 1 MATERIALS AND FINISH:
-DOME: PC, COLOR: TRANSPARENT SMOKE
-MODULE BASE: PBT, COLOR: GREY
-O-RING: SILICONE
-CONTACTS: BRASS, FINISH: Sn
-PCBA: FR4
2. MUST COMPLY WITH DIRECTIVE 2011/65/EU (ROHS)
- 3 MATES WITH ZHAGA BOOK 18 RECEPTACLES,
SEE TE LUMAWISE ENDURANCE S/S2; P/N: 2213858-X, 2363638-X
- 4 PRODUCT IDENTIFICATION LABEL



H	2410739-9
J	2410739-8
F	2410739-7
Q	2410739-6
P	2410739-5
D	2410739-4
C	2410739-3
B	2410739-2
A	2410739-1
ASTROLOCK VERSION	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. MOSTOLLER 29SEP2023	TE Connectivity			
DIMENSIONS: mm		CHK M. MOSTOLLER 29SEP2023				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD -	NAME ALR-11000 STREETLIGHT DIGITAL PHOTOCELL			
		PRODUCT SPEC 108-160585	-			
		APPLICATION SPEC 114-160342	SIZE A2			
MATERIAL SEE NOTE 1	FINISH	WEIGHT -	CAGE CODE 00779	DRAWING NO C-2410739	RESTRICTED TO -	
-		CUSTOMER DRAWING		SCALE 1:1	SHEET 1 OF 1	REV A