







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	Initial production release	19-MAR-24	GVA	WZ

RoHS2.0+HF



2480843-1



NOTES:

SPECIFICATION:

- CURRENT RATING: 3.0A MAX
- VOLTAGE: 20V AC/DC
- TEMPERATURE RANGE: -30 °C ~ 85 °C
- CONTACT RESISTANCE: 40 MILI OHM MAX
- INSULATION RESISTANCE: 100 MEGA OHM MIN.
- INSERTION FORCE : 5N~20N
- UNMATING FORCE: 8N~20N,AFTER DURABILITY TEST: 6N~20N.
- DURABILITY: 10000 CYCLES


PIN	SIGNAL NAME	NO.	DESCRIPTION	MATERIAL	REMARKS	QTY
B12	GND					
B9	VBUS					
B5	CC2	3	SHELL	STAINLESS STEEL	Ni: 30u" Plated	1 PC
A5	CC1					
A9	VBUS	2	CONTACT	COPPER ALLOY	Contact Area: Au 3u" Solder Area: Gold flash Over All: Ni 30u"Min	1 SET
A12	GND	1	HOUSING	HIGH TEMPERATURE PLASTIC	BLACK,UL94 V-0	1 PC

PCB HOLES(TOP VIEW) t=1.0mm
 TOLERANCE UNSPECIFIED ±0.05mm
 Recommended PCB thickness : 08-1.0 mm (nominal)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	12JAN2024	TE Connectivity	
		CHK	12JAN2024		
		WenKe He		NAME	
		Will Zi		PRODUCT SPEC	
		12JAN2024		APPLICATION SPEC	
		108-161210		SIZE	
				CAGE CODE	
				DRAWING NO	
				RESTRICTED TO	
		0.42g		A2 00779 C-2480843	
		CUSTOMER DRAWING		SCALE 1:1 SHEET 1 OF 2 REV A	


RoHS2.0+HF

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-




- NOTES 1:
1. IF THERE ARE EMPTY ZERO BOXES, THEY MUST BE FILLED WITH BUFFER MATERIALS.
 2. HANDLE WITH CARE DURING HANDLING.
 3. DURING TRANSPORTATION, DO NOT STACK TOO MUCH AND DO NOT HAVE HEAVY PRESSURE.
 4. THE UPPER TAPE MUST BE FLAT WHEN STICKING THE LOWER TAPE, AND THERE SHALL BE NO BUBBLES AT THE STICKING PLACE.
 5. SEAL THE CARTON WITH TAPE;
 6. ATTACH THE LABEL TO THE SIDE OF THE CARTON.
 7. Reel : 1300pcs/ Reel.
 8. Carton : 14300pcs/ 11 Reel/ Carton.

PCS/REEL	PCS/CARTON
1300	14300



- NOTES 2:
1. PACKAGE MATERIAL IN PLASTIC, RUBBER, INK, PIGMENT AND PAINT MUST MEET CONTROLLED SUBSTANCES SPEC PER 230-702.
 - *CADMIUM AND CADMIUM COMPOUNDS NOT TO EXCEED: 5 PPM.
 - *LEAD, CADMIUM, CHROM VI AND MERCURY NOT TO EXCEED: 100 PPM (COMBINED).
 - *CARRIER TAPES, COVER TAPES, REELS AND TAPED COMPONENTS MUST MEET THE REQUIREMENTS DERIVED PER EIA-481-C.
 2. MATERIAL:
 - COVER TAPE: PET, COLOR: TRANSPARENT
 - CARRIER TAPE: SYNTHETIC MATERIALS, COLOR: TRANSPARENT.
 - REEL: PS BLUE
 - SHIPPING BOX: CORRUGATED FIBER
 3. PACKAGE SPECIFIED REFER TO PER EIA-481-D.
 4. WATERPROOF AND MOISTURE-PROOF PACKING.
 5. SELF-ADHESIVE COLD SEAL



SCHEMATIC DIAGRAM OF CARDBOARD BOX WITH TE LOGO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	12JAN2024	TE Connectivity	
		CHK	12JAN2024		
		WenKe He		NAME	
		Will Zi		PRODUCT SPEC	
		108-161210		USB-C,6 Pin,Mid mount,3uGF L=6.8mm	
		APPLICATION SPEC		RESTRICTED TO	
		WEIGHT	0	SIZE	A2
		CAGE CODE		00779	DRAWING NO
		C-2480843		SCALE	
		CUSTOMER DRAWING		1:1	SHEET
				2 OF 2	REV
					A

2480843