


REVISIONS

P	LTR REV	DESCRIPTION MODIFICATIONS	DATE	DWN DESS.	APVD APP.
	B	Mise à jour suite à chgt version	19MAY2022	JB	GN

CAPACITES : Neutre porteur 54.6 à 70mm² (NFC33-209)

CAPACITIES : Neutral messenger 54.6 to 70 sqmm



- Charge de rupture: 18,45kN
Minimum breaking load: 18.45kN

EAD 2000 DT 68-25-042	2832100-1	68-25-042
DESCRIPTION	PART NUMBER	CODET Enedis

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
TOLERANCES NON SPECIFIEES: -

FINISH
FINITION -

DIMENSIONS:

mm

DWN / DESSINE
J. BERLAND

25-May-22

MATERIAL
MATIERE -

CHK / VERIFIE -

APVD / APPROUVE
G. NEDELLEC

PRODUCT SPEC
SPEC. PRODUIT -

APPLICATION SPEC
SPEC. APPLICATION -

WEIGHT
MASSE APPROX. -

NAME
TITRE

EAD 2000 DT 68-25-042

SIZE
FORMAT

A4

CAGE CODE

DRAWING NO
No PLAN

C-2832100

RESTRICTED TO
RESERVE A

-

CUSTOMER DRAWING

/PLAN CLIENT

UNIQUEMENT
POUR REFERENCE

SCALE
ECHELLE -

SHEET
FEUILLE

OF
DE

REV

B

LIBRE A LA DIFFUSION

TOUS DROITS RESERVES.

© 2022 Tyco Electronics Corporation. All Rights Reserved.

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
TOLERANCES NON SPECIFIEES:
(SUIV NB DE DECIMALES):

0 PLC / DEC: ±
1 PLC / DEC: ±0.1
2 PLC / DEC: ±0.01
3 PLC / DEC: ±0.001
4 PLC / DEC: ±0.0001
ANGLES ±

