








THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION, ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
DS	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
		A		RELEASED	15NOV.'06	SC	JK
		A1		REVISED PER ECR-20-100514	20OCT'20	MG	DZ



	368577-6	 PC/PET UL94 V-0	BLUE
OBSOLETE	368577-4		YELLOW
OBSOLETE	368577-2		RED
	368577-1		NATURAL
	Part NO.	MATERIAL	COLOR

- NOTES:
1. APPLICABLE CONTACT P/N,
REC CONTACT: 177915-X (AWG20~AWG16)
177914-X (AWG26~AWG22)
 2. MATING CONN. P/N,
CAP HOUSING: 179467-X (FREE HANGING)
TAB CONTACT: 177917-X (AWG20~AWG16)
177916-X (AWG26~AWG22)
 3. APPLICABLE PLATE P/N: 177920-X
 4. GENERAL TOLERANCES: ±0.25, ±3°
-  GLOW WIRE TEST AT 750°C WITHOUT FLAME.

<small>THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.</small>		tyco <i>Electronics</i>		AMP KOREA. kyungsan, korea	
DIMENSIONS: MM 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± MATERIAL - FINISH -		NAME: PDL 8P PLUG HSG 3.96mm DBL ROW(GWT) SIZE: A3 CAGE CODE: 00779 C= DRAWING NO: 368577 WEIGHT: -	
DWN: SC KIM CHK: BW KNAG APVD: JK SONG PRODUCT SPEC: 108-5410 APPLICATION SPEC: 114-5175		CUSTOMER DRAWING		RESTRICTED TO: - SCALE: N.S SHEET: 1 OF 1 REV: A1	