


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION, 19 .  
 © COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

PROD 4092 CODE	LOC DF	DIST S0	P	F	REVISIONS				
					ZONE	LTR	DESCRIPTION	DATE	APPD
						A	ADD -3 PER 0600-8044-98 CT	12-98	DE



- 1. TOLERANCE OF LEAD LENGTH:  
 UP TO 24 INCHES [609.6] = ±.12 [±3.0]  
 24 INCHES [609.6] & UP = ±1%
- 2. MARKED PER MIL-STD-130.
- 3. TO MATE WITH AMP LGH-1/2L RECEPTACLE WITH .89 [22.6] BARREL DEPTH.
- 4. OPERATING VOLTAGE: 15 KVDC AT 0 TO 70,000 FEET, -55°C TO 125°C.

80.00 [2032.0]	445046-3
18.00 [457.2]	445046-2
24.00 [609.6]	445046-1
A DIM 1	PART NO.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES [mm] TOLERANCES ON: 2 PLC DEC ± .02 [0.5] 3 PLC DEC ± - ANGLES ± -	DR 2-12-90 C.C. THOMAS
	CHK 2-12-90 M. GARDNER
MATERIAL SEE CALLOUTS	APPD 2-12-90 M. GARDNER
	RLSE 2-12-90 C.C. THOMAS
FINISH SEE CALLOUTS	PRODUCT SPEC -
	APPLICATION SPEC -
	WEIGHT -

AMP INCORPORATED Harrisburg, Pa. 17105		
NAME LEAD ASS'Y, POS STOP, DBL. END, LGH-1/2L (BROWN)		
SIZE <b>B</b>	CAGE CODE 00779	DRAWING NO 445046
SCALE 2:1	SHEET 1 OF 1	