

4

3

2

1




© - TE Connectivity. All Rights Reserved.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-


LOW HALOGEN

DIRECTION OFF TOP OF REEL



DETAIL B

POLYIMIDE COVER



△	△	700	16	11	61.8	88	84.4	42.2	140	9-5177985-6
FINISH	QTY	F	E	D	C	B	A	POS	PART NO.	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: SK LEAW CHK: ERIC TNG APVD: SF LEONG		17MAY2004	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± 0.3 2 PLC ± 0.25 3 PLC ± 0.2 4 PLC ± - ANGLES ± -		NAME: SF LEONG	
MATERIAL: -		FINISH: -		PRODUCT SPEC: 108-5390	
				APPLICATION SPEC: 114-5254	
				WEIGHT: -	
				CUSTOMER DRAWING	
				SIZE: A2	
				CAGE CODE: 00779	
				DRAWING NO: C=5177985	
				RESTRICTED TO: -	
				SCALE: 1:1	
				SHEET: 2 of 4	
				REV: R5	

4

3

2

1

© - TE Connectivity. All Rights Reserved.

DIRECTION OFF TOP OF REEL







8-5177985-5

8-5177985-1

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

USER DIRECTION OF UNREELING →

DETAIL A
(SCALE 4-1)WINDING THE COVER TAPE
AROUND THE OUTER
PERIPHERY IN A TURN.

A-A

B-B

LOW HALOGEN

WITHOUT COVER

△	700	16	22.2	44	40.4	20.2	40	8-5177985-1
△	700	16	53.8	72	68.4	34.2	120	8-5177985-5
FINISH	QTY	F	D	C	B	A	POS	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN: SK LEAW 17/MAY/2004

CHK: ERIC TNG

APVD: SF LEONG

PRODUCT SPEC

108-5390

APPLICATION SPEC

114-5254

WEIGHT

CUSTOMER DRAWING

TE

TE Connectivity Ltd.

RECEPTACLE ASSEMBLY 5H TYPE
(0.5MM BOSS LENGTH) FOR 0.8FH
ON TAPING

SIZE: A2 CAGE CODE: 00779 DRAWING NO: 5177985

RESTRICTED TO: -

SCALE: 1:1 SHEET: 3 of 4 REV: R5

4

3

2



1

© - TE Connectivity. All Rights Reserved.




LOW HALOGEN

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



SECT. "A" - "A"
(SCALE 10-1)



RECOMMENDED P.C. BOARD LAYOUT

CONNECTOR ONLY

20.2	21.8	15.2	40	8-	-1
52.2	53.8	47.2	120	8-	-5
68.2	69.8	63.2	160	9-	-8
52.2	53.8	47.2	120	9-	-5
44.2	45.8	39.2	100	9-	-4
36.2	37.8	31.2	80	9-	-3
28.2	29.8	23.2	60	9-	-2
20.2	21.8	15.2	40	9-	-1
84.2	85.8	79.2	200	2-	-0
76.2	77.8	71.2	180	1-	-9
68.2	69.8	63.2	160	1-	-8
60.2	61.8	55.2	140	1-	-6
52.2	53.8	47.2	120	1-	-5
44.2	45.8	39.2	100	1-	-4
36.2	37.8	31.2	80	1-	-3
28.2	29.8	23.2	60	1-	-2
20.2	21.8	15.2	40	1-	-1
84.2	85.8	79.2	200	1-	-0
76.2	77.8	71.2	180		-9
68.2	69.8	63.2	160		-8
60.2	61.8	55.2	140		-6
52.2	53.8	47.2	120		-5
44.2	45.8	39.2	100		-4
36.2	37.8	31.2	80		-3
28.2	29.8	23.2	60		-2
20.2	21.8	15.2	40		-1
C	B	A	POS	PART NO.	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: SK LEAW CHK: ERIC TNG APVD: SF LEONG	17MAY2004	TE Connectivity Ltd.	
DIMENSIONS: mm		PRODUCT SPEC: 108-5390		RECEPTACLE ASSEMBLY 5H TYPE (0.5MM BOSS LENGTH) FOR 0.8FH ON TAPING	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC: 114-5254		RESTRICTED TO	
MATERIAL: -		WEIGHT: -		SCALE: 1:1	
FINISH: -		CUSTOMER DRAWING		SHEET 4 of 4	
0 PLC ± - 1 PLC ± 0.3 2 PLC ± 0.25 3 PLC ± 0.2 4 PLC ± - ANGLES ± -		SIZE: A2 CAGE CODE: 00779 DRAWING NO: C=5177985		REV: R5	