


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
AF	50	P	LTR	DESCRIPTION	DATE	DWN	APVD
		E		REVISED PER ECR-13-004343	30JUL13	KH	KR



- 1 MATES WITH .020±.001 X .187 TAB
- 2 WIRE SIZE 22-18 AWG, STRIP LENGTH .281 LONG.
- 3 INSULATION SIZE IS .230 MAX DIA.
- 4 DIMENSION DOES NOT INCLUDE TRIM BURR.
- 5 .015 MAX CARRIER TRIM BURR PER SIDE IS ALLOWABLE IN THE SHADED AREA.

HOUSING: NYLON, COLOR-RED TRANSLUCENT RECEPTACLE: BRASS, TIN	2-520262-2
MATERIAL & FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 03DEC02	TE Connectivity RECEPTACLE ASSY, ULTRA-FAST, 187 SERIES, LOOSE PIECE WIRE SIZE: 22-18 AWG				
DIMENSIONS: INCHES		CHK J HUMMEL 03DEC02					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J HUMMEL 03DEC02					
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .015 4 PLC ± - ANGLES ± -		NAME					
MATERIAL SEE TABLE		FINISH SEE TABLE	PRODUCT SPEC 108-2043	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
			APPLICATION SPEC 114-2123	A3	00779	C-520262	-
			WEIGHT -	CUSTOMER DRAWING			SCALE 4:1
			SHEET 1 OF 1		REV E		