



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AI	-						

Kontakt Contact	DGB (mm^2) Wire Range	Drahtcrimp/Wirecrimp		Isocrimp	Iso.-Ø	Betriebsanl.
		Hoehe/Height	Breite/Width	Breite/Width	Ins. Range	Instr. Sheet
965858 / 965861	4.0	2.50	3.56	4.50	3.4-3.7	411-18225
965859 / 965862	6.0	2.88	4.06	5.10	4.0-4.3	



539754-2	1	2-539787-0	locator ass.	Positioniereinheit	A
	1	0-539786-6	contact guide	Kontaktabstuetzung	A
	1	1-519151-3	screw M4x25	Schraube M4x25	A
	1	1-519151-1	screw M4x16	Schraube M4x16	A
	1	0-519024-2	hex nut M4	Mutter M4 DIN 985	A
	1	0-519021-8	hex nut M4	Mutter M4 DIN 934	A
	QTY Stck	PN	Description	Benennung	REV

DIMENSIONS: mm-DIN 7168-m		DWN M.Weberndoerfer 17JAN2000	MATERIAL -		FINISH -			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		CHK U.Reuter 17JAN2000	AMP tyco Electronics AMP GmbH D - 64625 Bensheim					
		APVD -						
		PRODUCT SPEC -	NAME ERGOCRIMP Die Set for Ø4.0 mm					
		APPLICATION SPEC -						
		WEIGHT -	SIZE A4	CAGE CODE 00779	DRAWING NO C=539754-2	RESTRICTED TO -		
		CUSTOMER DRAWING			SCALE 2:1	SHEET 1 OF 1		
					REV A			