


DESCRIPTION	MATERIAL	FINISH
MODULE ASSEMBLY	THERMOSET EPOXY	COLOR: BLACK
GROMMET	FLOURSILICONE 40/50 PER MIL-R-25988	COLOR: NATURAL
CONTACT SOCKET	BERYLLIUM COPPER ASTM-B194	GOLD PLATE PER MIL-G-45204
RETAINING CLIP	BERYLLIUM COPPER ASTM-B194 OR STAINLESS STEEL PER QQ-S-766	NONE



P	LTR	DESCRIPTION	DATE	OWN	APVD
K		REV PER ECN-24-271664	21JUN2024	LP	YL

- 1 MARK MODULE IDENTIFICATION, "AMP", AMP PART NO. AND DATE CODE .060 MINIMUM HIGH CHARACTERS PER 115-10002-2.
- 2 MARK MODULE WITH SCHEMATIC DIAGRAM AT AREA SHOWN PER 115-10002-2.
- 3 MARK MODULE 591863-3 WITH CUSTOMER PART NO. 204-16164-3 PER 115-10002-2.
- 4 DIODE MAY BE A COMMERCIAL DIODE THAT HAS BEEN SCREENED TO MEET THE REQUIREMENTS OF JANTX1N5552.
- 5 MARK MODULE 591863-2 WITH CUSTOMER P/N DSC254-1
- 6 P/N 591863-3 INCLUDES 11 PIN CONTACTS, P/N 2-592404-1 PACKAGED SEPARATELY

BUSSING ARRANGEMENT



INDEXING INDICATOR



SCHEMATIC DIAGRAM

NOTES	QTY OF DIODES	DIODE	PART NO.
	5	JANTX1N4007	591863-4
3 6	5	JANTX1N5552 4	591863-3
5	5	JANTX1N5552 4	591863-2
	5	JANTX1N5552 4	591863-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN C.C. THOMAS 6-6-03		NAME MODULE ASSY, FEEDBACK, SIZE 20, TJ
CHK D. EABY 6-6-03		
APVD D. EABY 6-6-03		
PRODUCT SPEC		
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APPLICATION SPEC
0 PLC ± -	1 PLC ± -	
2 PLC ± -	3 PLC ± .005	
4 PLC ± -	ANGLES ± -	
MATERIAL	FINISH	WEIGHT
CUSTOMER DRAWING		SCALE 2:1 SHEET 1 OF 1 REV K