



MIN AREA FOR INHIBITOR

MIN AREA FOR INHIBITOR (TYP)

MAX AREA FOR INHIBITOR

NOTE:
 1. APPLY INHIBITOR BEFORE INSERTING BAIL IN "C"
 2. INHIBITOR 3/64 MAX THICK

REV	PER	BY	DATE	DESCRIPTION
B	REV PER EGN	EG	2-24-69	15112/17
C	REV PER G-0153	112	4-11-69	15112/17
B	REV	U	4-11-69	15112/17
A	602555 WAS 378417	E	4-11-69	15112/17
O	NPS 68-1533 (REV 1)		4-11-69	15112/17

QTY	DWG	NUMBER	NAME	REMARKS	ITEM NO
1		602103-1	BAIL	WIRE SIZE 4/0	4
1		277141-2	WEDGE		3
1		602145-2	"C"		2
1		80665-1	INHIBITOR		1

REQUIRED PER ASSEMBLY		MATERIAL	HEAT TREAT	COATING OR PLATING
WIRE RANGE	477.0			
AREA				
CLASS				
TYPE	LARGE			

DATE	BY	FIRST USED	SCALE	NAME
6-10-69	Len Gyles			
6-12-69	R. P. Gyles			
6-12-69	W. H. Gyles			
8-12-69	M. E. Gyles			

NO	DESCRIPTION	REV
1	AMP INCORPORATED HARRISBURG PENNA	
2	NO 602247	
3	AMPACT STIRRUP ASSY	

LOC B6 DIST 1