


LOC	DIST	REVISIONS					
IJ	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
		A		INITIAL ISSUE	24 AUG 05	MGR	DB



NOTES:

- ATTENUATION $\leq 0,5$ dB(MT-RJ) AND $\leq 0,3$ dB(SC), MEASURED AT 1300nm ACC. TO IEC 61300-3-4 EQUILIBRIUM MODE CONDITION
- INDIVIDUAL LENGTH DIFFERENCE ON SC SIDE ≤ 5 mm
- SUPPLY FILLED OUT TEST RESULT SHEET WITH EACH INDIVIDUALLY PACKED ASSEMBLY
- DAT LABEL INFO:
 - UNIQUE SERIAL NUMBER
 - TYCO LOGO PN
 - MANUFACTURING LOCN.
- CROSS OVER AS PER BELOW TABLE

FIBRE COLOR	LEFT CONN.	RIGHT CONN.
WHITE	SC A	MT-RJ B
BLUE	SC B	MT-RJ A

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (Meter)
X-6206615-Y	XY,0
8-6206615-9	9,5
9-6206615-0	0,5
9-6206615-1	1,5
9-6206615-2	2,5
9-6206615-3	3,5
9-6206615-4	4,5
9-6206615-5	5,5
9-6206615-6	6,5
9-6206615-7	7,5
9-6206615-8	8,5

1	-	FOAC DAT-85 LABEL ON REEL	16
1	-	DUST COVER, MT-RJ	15
1	-	HOUSING, CONN, MT-RJ, BLACK	14
1	-	MT/RJ FERRULE, THERMOPLAST, MM	13
1	-	PIN KEEPER, 3.8MM	12
1	-	SPRING, MT-RJ, 3.8 DESIGH	11
1	-	MT-RJ, SPRING PUSH, UNIVERSAL	10
1	-	CRIMP EYELET, MT-RJ	9
1	-	MT-RJ BOOT, TWIN ZIP BEIGE	8
2	-	PROTECTIVE COVER, 2.5MM, BLACK	7
1	-	SC DUPLEX HOUSING. BEAM HALF	6
1	-	SC DUPLEX HOUSING, RET. PLATE HALF	5
2	-	SC CERAMIC, OVERMOLDED	4
2	-	CRIMP EYELET, SC, 2.0MM PLATED	3
2	-	FOAC BOOT 2.0 BLACK SC/FC	2
L	-	FOCAB 1.8MZ T 62.5/125 GREY LSZH	1
Qty	Part Number	Description	Item

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	GIRIYAPPA. M	24 AUG 05	Tyco Electronics Corporation FOBU, Bangalore, India
CHK	DIWAKAR BELAVADI	24 AUG 05	
APVD	DIWAKAR BELAVADI	24 AUG 05	
PRODUCT SPEC			
APPLICATION SPEC			NAME
DIMENSIONS: mm TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH -			FOMM62,5 LEAD 1,8MTZ SC/PC-MTRJ SIZE: A2 CAGE CODE: 00779 DRAWING NO: C=6206615 RESTRICTED TO: - SCALE: NTS SHEET 1 OF 1 REV: A
MATERIAL: -			CUSTOMER DRAWING