


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
D		ECR-16-008648	17JUN2016	WZ GG



DB9 F	DB9 F
P1	P2
2	3
3	2
4	1
	6
5	5
6	4
1	
7	8
8	7
SHELL	SHELL

PART NO.	"L"(IN)	TOL.(IN)	LABEL XX'	
621850-1	72.00	+6.00/-2.00	6	OBSOLETE
621850-2	120.00	+6.00/-2.00	10	
621850-3	180.00	+6.00/-2.00	15	OBSOLETE

- 1. 28 AWG, STRANDED TINNED COPPER, 7 COND WITH DRAIN, 100% ALUMINUM MYLAR FOIL PLUS 10% NOMINAL OVERLAP, BEIGE.
- 2. PACKAGED IN PRINTED ZIPLOCK POLYBAG.
- 3. LABEL ON POLYBAG TO READ AS FOLLOWS:  

621850-__	PART NO.
XX' DB9 F/F NULL MODEM/SERIAL COUNTRY OF ORIGIN	XX' = LENGTH PER TABLE
- 4. POSN'S 1 & 6 JUMPERED TOGETHER AND CONNECTED TO POSN 4.
- 5. THIS PRODUCT IS PRODUCED IN COMPLIANCE WITH ANSI/ASQC Z1.4-1993, TO AN INSPECTION LEVEL III, WITH A NORMAL SAMPLING PLAN.
- 6. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230-702.

#4-40 SLOTTED THUMBSCREW	4
OVERMOLD, PVC, BEIGE	3
CONNECTOR, DB9, FEMALE	2
CABLE, 7 CONDUCTOR	1
DESCRIPTION	ITEM NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.EISENTRAUT 11-20-96	<b>STE</b> TE Connectivity	
DIMENSIONS: INCHES		CHK D.WILSON 11-21-96		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R.CAPP 11-21-96	NAME CABLE ASSY, DB9 TO DB9 (FEMALE), OVERMOLDED	
0 PLC ± -		PRODUCT SPEC	SIZE CAGE CODE DRAWING NO RESTRICTED TO	
1 PLC ± -		APPLICATION SPEC	A2 00779 C=621850	
2 PLC ± -			SCALE SHEET 1 of 1 REV D	
3 PLC ± -				
4 PLC ± -				
ANGLES ± -				
FINISH		WEIGHT 0.000000		
MATERIAL		RESTRICTED CUSTOMER		