


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
CF	39	REV PER OB20-1505-97	10/29/97	DKE	MT

- ① DATE CODE AND MANUFACTURING LOCATION MARKED ON LABEL.
- ② OBSOLETE PART NUMBER.



WIRE COLOR CHART

P1		P2	P1		P2
PIN NO	WIRE COLOR	PIN NO	PIN NO	WIRE COLOR	PIN NO
50	PINK/ORANGE	50	37	TAN/ORANGE	37
25	ORANGE/PINK	25	12	ORANGE/TAN	12
49	BROWN/GRAY	49	36	TAN/PINK	36
24	GRAY/BROWN	24	11	PINK/TAN	11
48	BROWN/VIOLET	48	35	TAN/BROWN	35
23	VIOLET/BROWN	23	10	BROWN/TAN	10
47	BROWN/BLUE	47	34	WHITE/GRAY	34
22	BLUE/BROWN	22	9	GRAY/WHITE	9
46	BROWN/GREEN	46	33	WHITE/VIOLET	33
21	GREEN/BROWN	21	8	VIOLET/WHITE	8
45	BROWN/YELLOW	45	32	WHITE/BLUE	32
20	YELLOW/BROWN	20	7	BLUE/WHITE	7
44	BROWN/ORANGE	44	31	WHITE/GREEN	31
19	ORANGE/BROWN	19	6	GREEN/WHITE	6
43	BROWN/PINK	43	30	WHITE/YELLOW	30
18	PINK/BROWN	18	5	YELLOW/WHITE	5
42	TAN/GRAY	42	29	WHITE/ORANGE	29
17	GRAY/TAN	17	4	ORANGE/WHITE	4
41	TAN/VIOLET	41	28	WHITE/PINK	28
16	VIOLET/TAN	16	3	PINK/WHITE	3
40	TAN/BLUE	40	27	WHITE/BROWN	27
15	BLUE/TAN	15	2	BROWN/WHITE	2
39	TAN/GREEN	39	26	WHITE/TAN	26
14	GREEN/TAN	14	1	TAN/WHITE	1
38	TAN/YELLOW	38			
13	YELLOW/TAN	13			

	256.00	+6.00	-0.00	2-750254-0
	197.00	+4.00	-0.00	1-750254-9
	30.00	+1.00	-0.00	1-750254-8
	984.25	+24.00	-0.00	1-750254-7
	12.00	+1.00	-0.00	1-750254-6
OBSOLETE	22.10	+1.00	-0.00	1-750254-5
OBSOLETE	20.90	+1.00	-0.00	1-750254-4
	18.00	+1.00	-0.00	1-750254-3
OBSOLETE	15.00	+1.00	-0.00	1-750254-2
	13.12	+1.00	-0.00	1-750254-1
	58.00	+4.00	-0.00	1-750254-0
	393.70	+6.00	-0.00	750254-9
	590.55	+6.00	-0.00	750254-8
	300.00	+6.00	-0.00	750254-7
	180.00	+4.00	-0.00	750254-6
OBSOLETE	120.00	+4.00	-0.00	750254-5
	39.36	+2.00	-0.00	750254-4
	118.08	+4.00	-0.00	750254-3
	78.72	+4.00	-0.00	750254-2
	24.00	+1.00	-0.00	750254-1
	A			PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DWN V. COLLER 3-26-97	AMP Incorporated Harrisburg, PA 17105-3608
		CHK D. WILSON 3-26-97	
		APVD D. WILSON 3-26-97	NAME
		PRODUCT SPEC	CABLE ASSY, 50 POSN, STRAIGHT EXIT, .050 SERIES AMPLIMITE
		APPLICATION SPEC	
MATERIAL	FINISH	WEIGHT	SIZE CAGE CODE DRAWING NO RESTRICTED TO
			A2 00779 C=750254
CUSTOMER DRAWING			SCALE SHEET 1 OF 1 REV R