


Schraube 2+1 mm
in Längsrichtung
beweglich.
Übertragbare Anzugs-
und Abdruckkraft
mindestens 300N
(Prüfwert)

⚠ 5-10µm VERZINKT
UND GOLD CHROMATIERT



OBSOLETE	825 274-1	Polyamid 6.6	natur
	Nummer	Werkstoff	Farbe

1	C	1-925251-0	10 pol. Gehäuse	Polyamid / natur	2
1	A	825276-2	Hebeschraube M4	9S20K 1 ⚠	1
			WERKSTOFF / OBERFLÄCHE		ITEM NO

L1	REVISED PER ECR-20-005366	SS	DL	14APR2020	QUANT	DWG SIZE	NUMBER	NAME	WERKSTOFF / OBERFLÄCHE	ITEM NO
L	68,8 ±0,5	WAR 68,8 ±0,5		26.2.94						
K	MASS 18:25	WAR 18,3 MAX		25.3.81						
I	⚠ WAR KADMIERT									
H	68,8 ±0,1	WAR 69 ±0,1		652 10.78						
S	-0,1 bei 6,2	hier		11.2.75						
F	18,3 max.	war 20,3 max.		165 4.1.79						
E	WAR 1-825274-1			142 8.14.79						
D	20,3 max.	war 20,3 ±0,3		9.73						
C	Schraube geändert			2.4.48						
B	Polarisation	hinzu gefügt		2.79						
A	69 war 69,5; 60,3 war 60,8			2.73						
LTR	REVISION RECORD				OR	CHK	DATE			

REQUIRED PER ASSEMBLY	DESCRIPTION

© 1972 BY AMP INCORPORATED. ALL RIGHTS RESERVED.
AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.

DR: 14.12.72

CHK: K

CLASS: SERIE 4,8 F.F.

TOLERANCE EXCEPT AS NOTED: ±0,05 ±1° 0'

SCALE: 2:1

LOC: A1 NO: B NO: 825 274

NAME: 10 pol. Steckhülsen-Gehäuse

CUSTOMER COPY REFERENCE ONLY

Deutsche AMP G.m.b.H.
Langen b. Ffm.
Germany

ZEICHNUNG GÜLTIG AB ...02/81

DIMENSIONS IN MILLIMETERS DO NOT SCALE PRINT.