



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	7	ECR-22-160088	06DEC2022	RB	SPS
	6	ECR-10-025774	29JAN11	KK	HMR

- ① STECK- UND LÖTSEITE: MIN. 4µm GALVAN. ZINN ÜBER 1.27µm NICKEL
- ② OBSOLETE
- ③ OBSOLETE

POLZ. PRO REIHE	L±0.4	BESTELL-NR.
-	-	-
2	5.08	827 270-2
3	7.62	-3
4	10.16	-4
5	12.70	-5
6	15.24	-6
7	17.78	-7
8	20.32	-8
9	22.86	-9
10	25.40	1-
11	27.94	1-
12	30.48	1-
13	33.02	1-
14	35.56	1-
15	38.10	1-
16	40.64	1-
17	43.18	1-
18	45.72	1-
19	48.26	1-
20	50.80	2-
21	53.34	2-
22	55.88	2-
23	58.42	2-
24	60.96	2-
25	63.50	2-
26	66.04	2-
27	68.58	2-
28	71.12	2-
29	73.66	2-
30	76.20	3-
31	78.74	3-
32	81.28	3-
33	83.82	3-
34	86.36	3-
35	88.90	3-
36	91.44	3-
37	93.98	3-
38	96.52	3-
39	99.06	3-
40	101.60	4-
41	104.14	4-
42	106.68	4-
43	109.22	4-
44	111.76	4-
45	114.30	4-
46	116.84	4-
47	119.38	4-
48	121.92	4-
49	124.46	4-
50	127.00	5- 827



KONTAKTSTIFT	Cu Sn	①
STIFTGEHÄUSE	PBTP GV	GRÜ
BENENNUNG	WERKSTOFF	OBERFLÄCHE FARBE

TE Connectivity. All Rights Reserved.

OBSOLETE

DIMENSIONS: mm		DWN: 3.89	MATERIAL: PBTP GV	FINISH: -	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK: SCHAAR.	TE Connectivity		
0 PLC ± - 1 PLC ± - 2 PLC ± 0.2 mm 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD: -			
PRODUCT SPEC: -		NAME: AMPMODU II STIFTLAISTE ZWEIREIHIG			
APPLICATION SPEC: -		SIZE: A4	CAGE CODE: 00779	DRAWING NO: 827270	RESTRICTED TO: -
WEIGHT: 0.000000		CUSTOMER DRAWING			
		SCALE: 4:1	SHEET: 1 OF 1	REV: 7	