

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
E		Contact pin material change from CuSn to CuZn	13SEP2017	KJK	PS

NOTES:

△1 Min3.0µm TIN OVER 1.27µm NICKEL

△2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

POS. PER ROW	L±0.5	PART NUMBER
-	-	-
2	5.08	827 311-2
3	7.62	△2 - 3
4	10.16	△2 - 4
5	12.70	△2 - 5
6	15.24	△2 - 6
7	17.78	△2 - 7
8	20.32	△2 - 8
9	22.86	△2 - 9
10	25.40	△2 - 0
11	27.94	△2 - 1
12	30.48	△2 - 2
13	33.02	△2 - 3
14	35.56	△2 - 4
15	38.10	△2 - 5
16	40.64	△2 - 6
17	43.18	△2 - 7
18	45.72	△2 - 8
19	48.26	△2 - 9
20	50.80	△2 - 0
21	53.34	△2 - 1
22	55.88	△2 - 2
23	58.42	△2 - 3
24	60.96	△2 - 4
25	63.50	△2 - 5
26	66.04	△2 - 6
27	68.58	△2 - 7
28	71.12	△2 - 8
29	73.66	△2 - 9
30	76.20	△2 - 0
31	78.74	△2 - 1
32	81.28	△2 - 2
33	83.82	△2 - 3
34	86.36	△2 - 4
35	88.90	△2 - 5
36	91.44	△2 - 6
37	93.98	△2 - 7
38	96.52	△2 - 8
39	99.06	△2 - 9
40	101.60	△2 - 0
41	104.14	△2 - 1
42	106.68	△2 - 2
43	109.22	△2 - 3
44	111.76	△2 - 4
45	114.30	△2 - 5
46	116.84	△2 - 6
47	119.38	△2 - 7
48	121.92	△2 - 8
49	124.46	△2 - 9
50	127.00	△2 5-827 311 0



△1	CuZn	CONTACT PIN	3
△1	CuZn	CONTACT PIN	2
GREEN	PBT	PIN HOUSING	1
COLOR/ FINISH	MATERIAL	DESCRIPTION	ITEM NUM

THIS DRAWING IS UNPUBLISHED. © COPYRIGHT - TE Connectivity ALL RIGHTS RESERVED.

DIMENSIONS: mm TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2mm 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	DWN DAHLHEIMER 05.12.75	MATERIAL -	FINISH -
	CHK BOCK 05.12.75	TE Connectivity	
APVD -	NAME AMPMODU II PIN HEADER, 90 DEG		
PRODUCT SPEC -	SIZE A4	CAGE CODE 00779	DRAWING NO C=827311
APPLICATION SPEC -	RESTRICTED TO -		
WEIGHT -	CUSTOMER DRAWING -		
		SCALE 4:1	SHEET 1 OF 1
		REV E	