


LOC	DIST	REVISIONS						
DF	S0	P	LTR	DESCRIPTION	DATE	DWN	APVD	
			U	REV PER 0G3D-0222-03	1-04	CT	DE	



846718-4 ONLY
DIMENSIONS & CALLOUTS
THE SAME EXCEPT AS SHOWN

-	-	-	-	-	13.00 [330.2]	846718-5
OBSOLETE	12.00 [304.8]	1.50 [38.1]	1.50 [38.1]	.38 [9.7]	11.00 [279.4]	846718-4
OBSOLETE	-	1.12 [28.4]	2.12 [53.8]	.38 [9.7]	38.50 [977.9]	846718-3
-	-	.62 [15.7]	1.62 [41.1]	.38 [9.7]	34.25 [870.0]	846718-2
OBSOLETE	-	4.00 [101.6]	5.00 [50.8]	.38 [9.7]	42.00 [1066.8]	846718-1
REMARKS	DIM E	DIM D	DIM C	DIM B	DIM A	PART NUMBER

- ¹ TOLERANCE OF LEAD LENGTH:
UP TO 24 INCHES [609.6] = ±.12 [±3.0]
24 INCHES [609.6] & UP = ±1%
2. MARKED PER MIL-STD-130.
- ³ PIGTAILS ARE SOLDER DIPPED.
4. TO MATE WITH AMP LGH-1
RECEPTACLE WITH .88 [22.3] BARREL DEPTH.
5. OPERATING VOLTAGE: 20 KVDC AT 0 TO 70,000 FEET, -55° C TO 125° C.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 4-9-97	AMP Incorporated Harrisburg, PA 17105-3608						
DIMENSIONS: INCHES [mm]		CHK S.GLATFELTER 5-5-97	NAME						
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S.GLATFELTER 5-5-97	PRODUCT SPEC						
		—		LEAD ASSY,LGH-1					
		APPLICATION SPEC							
		—							
		—							
		—							
MATERIAL	FINISH	WEIGHT	—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
SEE CALLOUTS	SEE CALLOUTS	—	A2	00779	C-846718		—		
CUSTOMER DRAWING				SCALE	1:1	SHEET	1 OF 1	REV	U