

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

REVISIONS

© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

P	LTR	DESCRIPTION	DATE	DWN	APVD
D2		REV. BY ECO 16-006304	29APR2016	HC	WLS
D3		REV. BY ECO 17-000292	10JAN2017	HC	WLS
D4		REV. BY ECO 17-009641	05JUL17	HC	WLS
E		REVISED PER ECN-23-214009	22MAY2023	WLS	JS

1,0±0,1  
6,6±0,2  
6,4±0,2  
14,7

31,7  
12,4  
9,1  
13,2

3,8  
LOGO MARK  
1,0

1- INTERCHANGEABLE WITH PN-180924.

2- PA 6.6 HEAT STABILIZED.

3- PA 6.6 ACC. TO SPEC. IEC 60335-1, GWEPT 750°C WITHOUT FLAME.

NATURAL	3	1-880298-1
BLACK	2	1-880298-0
NATURAL	PA 6.6	880298-1
FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 27APR2016  
H.C. CANTERICHK 28APR2016  
W.L. STEFANI

APVD -

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±0,4
2 PLC	±-
3 PLC	±-
4 PLC	±-
ANGLES	±1°

MATERIAL -

FINISH -

NAME

2 WAY .250 FAST-IN-ON TAB HOUSING

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 - C-880298 -

SCALE 3:1 SHEET 1 OF 1 REV E

1470-19 (3/13)