


LOC F	DIST 7	REVISIONS			
P	LTR REV	DESCRIPTION MODIFICATIONS	DATE	DWN DESS.	APVD APP.
	-	-	-	-	-



- | | |
|---|---|
| 1. CONNECTOR, ITEM 1, FOLLOWING APPLICATION SPEC. 114-16015. | 1. LE CONNECTEUR, ITEM 1, SUIVANT SPEC. D'APPLICATION 114-16015. |
| 2. FOR SOLDERABILITY SEE AMP PRODUCT SPEC. 108-9024. | 2. POUR LA SOUDABILITE, VOIR SPEC. PRODUIT AMP 108-9024. |
| 3. DRAWING NOT TO SCALE. | 3. REPRESENTATION NON A L'ECHELLE. |
| △ 4 HOUSING, THERMOPLASTIC, BLACK. CONTACT, PHOS.BRONZE, BRIGHT TIN-LEAD OVER NICKEL. | △ 4 BOITIER, THERMOPLASTIQUE NOIR. CONTACT, PHOS.BRONZE, ETAMAGE BRILLANT SUR SOUS-COUCHE NICKEL. |
| △ 5 CONDUCTOR, COPPER ANNEALED. INSULATION, POLYESTER. | △ 5 CONDUCTEUR, CUIVRE GAINÉ, POLYESTER. |
| △ 6 SOLDER TAB, BRIGHT TIN-LEAD OVER NICKEL. | △ 6 CONTACT A SOUDER, ETAMAGE BRILLANT SUR SOUS-COUCHE NICKEL. |

14	88997-2	SOLDER CONTACT/CONTACT A SOUDER	△ 6	④
87mm	1-88586-3	CABLE, FFC .100 CENTERLINE, 14 COND.	△ 5	③
14	487406-4	FEMALE CONTACT/CONTACT FEMELLE	△ 4	①
1	1-487378-3	HSG, SGL ROW/BOITIER SIMPLE RANGEE, 14P		

ASSY 953234-1	PART NO/REFERENCE	DESCRIPTION	ITEM
QUANTITY PER ASSY	PARTS LIST / REFERENCES		

DIMENSIONS: Inch [mm]	DWN/DESSINE Françoise BLASCO 16-SEP-97	MATERIAL MATIERE	FINISH FINITION		
	CHK/VERIFIE Y.PETRONIN 17-NOV-97				
TOLERANCES UNLESS OTHERWISE SPECIFIED: TOLERANCES NON SPECIFIEES (SUIV NB DE DECIMALES): 0 PLG/DEC ± 1 PLG/DEC ±0.02 2 PLG/DEC ± [0.50] 3 PLG/DEC ± 4 PLG/DEC ± ANGLES ±-	APVD/APPROUVE Y.PETRONIN 17-NOV-97	AMP AMP DE FRANCE 95301 PONTOISE			
	PRODUCT SPEC SPEC. PRODUIT				
	APPLICATION SPEC SPEC. APPLICATION	NAME TITRE JUMPER 14 COND. LG=3.6"			
	WEIGHT MASSE APPROX.	SIZE FORMAT A4	CAGE CODE 00779	DRAWING NO TITRE C-953234	
CUSTOMER DRAWING/PLAN CLIENT		UNIQUEMENT POUR REFERENCE	SCALE ECHELLE 1:1	SHEET FEUILLE 1 OF 1 DE 1	REV 0

RELEASED FOR PUBLICATION

THIS DRAWING IS UNPUBLISHED.
DIFFUSION RESEINTE AMP

ALL RIGHTS RESERVED.
TOUS DROITS RESERVES.
BY AMP INCORPORATED.
COPYRIGHT 19