

THIS DRAWING IS UNPUBLISHED. VERTRAULICHE UNVEROEFFENTLICHTE ZEICHNUNG.
 BY AMP INCORPORATED. ALL RIGHTS RESERVED. ALLE RECHTE VORBEHALTEN.
 COPYRIGHT 19-

MATED WITH: PASSEND ZU:	LOC AI	DIST -	REVISIONS AENDERUNGEN DESCRIPTION BESCHREIBUNG				DATE	DWN	APVD
-	-	-	P	LTR					
PROJEKT NR.: -				A2	EG00 0587 98	27-MAY-98	T.B.	-	
				A3	CHANGED REMARK FROM "SEE 116-18014" TO "SEE 1355049"	18-MAY-00	M.P.	V.H.	

Customer Drawing

for PN 964326

SEE 1355049

-	-	-	-	-	-	-	-
CUSTOMER PART NO	AMP PART NO	REV.	PCS.	MATERIAL	SURFACE COLOR	DESCRIPTION	

DIMENSIONS: DIMENSIONEN: mm TOLERANCES UNLESS OTHERWISE SPECIFIED; ALLGEMEINTOLERANZEN n. ISO 8015 p. ISO 2768 - mH -E r. DIN 16901 - 140 p/PLC ±- p/PLC ±- p/PLC ±- p/PLC ±- ANGLES/WINKEL ±-	DWN T. Bensch 27-MAY-98 CHK V. Huhn 18-MAY-00 APVD M. Bleicher 19-MAY-00	MATERIAL - FINISH OBERFLAECHE/FARBE - AMP AMP Deutschland GmbH D - 63225 Langen
	PRODUCT SPEC PRODUKTSPEZ. - APPLICATION SPEC VERARBEITUNGSSPEZ. - WEIGHT GEWICHT -	NAME STANDARD-POWER-TIMER CONTACT TYP A STANDARD-POWER-TIMER KONTAKT TYP A SIZE A4 CAGE CODE 00779 DRAWING NO ZEICHNUNGS-NR. 964326 RESTRICTED TO NUR FUER -
CUSTOMER DRAWING /KUNDENZEICHNUNG		MASSSTAB - BLATT 1 OF 1 VON 1 A3

