


POS-NR.	Part	Material	Quantity
1	lower part	Al alloy tinned	1
2	upper part	Al alloy tinned	1
3	bolt M12 x 55	stainless steel	1
4	spring washer	stainless steel	1
5	o-ring	NBR quality, 70 shore A	1

Burr Projection:		DEBUR AND BREAK SHARP EDGES DIMENSION:	DO NOT SCALE DRAWING	REVISION: 1
FORM BOUND MEASURE:			This Information is confidential and proprietary to Tyco Electronics Corporation and its subsidiaries and affiliates. It may not be disclosed to anyone, other than Tyco Electronics personnel, without written authorization from Tyco Electronics Corporation, Harrisburg, Pennsylvania USA.	
NOT FORM BOUND MEASURE:			DESCRIPTION: <b>HEL-4812-KB; TCPN: 532410-000</b> Flat direct terminal clamp for single conductor 35-150 mm <sup>2</sup> with stainless steel bolt M12x55	
DRAWN	NAME	SIGNATURE	DATE	DWG NO. <b>C-HEL-4812-KB</b> SCALE: 1:1 SHEET: 1 OF 1
CHK'D				
APPV'D				
 <b>Tyco Electronics Raychem GmbH</b> a TE Connectivity Ltd. company Trachenbergring 85 12249 Berlin (Germany)				WEIGHT: 0,099kg