



	Description	Material
1	hexagon screw M12x55	stainless steel A2
2	spring washer 29x13x3	stainless steel A2
3	upper part HEL-4843 OT	high strength AL-alloy, corrosion-resistant, tin-plated
4	lower part HEL-4843 UT	high strength AL-alloy, corrosion-resistant, tin-plated
5	o-ring	NBR quality, 70 shore A

BURR PROJECTION:	DEBUR AND BREAK SHARP EDGES	DO NOT SCALE DRAWING	REVISION: 1
FORM BOUND MEASURE:	DIMENSION: mm	This Information is confidential and proprietary to Tyco Electronics Corporation and its subsidiaries and affiliates. It may not be disclosed to anyone, other than Tyco Electronics personnel, without written authorization from Tyco Electronics Corporation, Harrisburg, Pennsylvania USA.	
NOT FORM BOUND MEASURE:			

	NAME	SIGNATURE	DATE
DRAWN	S.Pollakowski		30.08.2021
CHK'D			
APPV'D			


Tyco Electronics Raychem GmbH
 a TE Connectivity Ltd. company
 Trachenbergring 85
 12249 Berlin (Germany)

DESCRIPTION:		HEL-4843-KB; PN:693600-000 FLAT DIRECT TERMINAL CLAMP for two conductors 35-150SM; 50-185SE; 35-70RM; 35-50RE	
DWG NO.		C-HEL-4843-KB	A4
WEIGHT:	0,114kg	SCALE:	1:1
		SHEET:	1 OF 1