


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	10JAN2024	AN	VN



PRODUCT DIMENSIONS

SIZE	AS SUPPLIED		AS RECOVERED							
	MINIMUM EXPANDED I.D. (D)		MAXIMUM RECOVERED I.D. (d)		WALL THICKNESS AFTER RECOVERY (W)					
					MINIMUM		MAXIMUM		NOMINAL	
	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.
3/64	1.17	.046	0.58	.023	0.43	.017	0.58	.023	0.50	.020
1/16	1.60	.063	0.79	.031	0.43	.017	0.58	.023	0.50	.020
3/32	2.36	.093	1.17	.046	0.43	.017	0.58	.023	0.50	.020
1/8	3.17	.125	1.57	.062	0.43	.017	0.58	.023	0.50	.020
3/16	4.74	.187	2.36	.093	0.56	.022	0.71	.028	0.63	.025
1/4	6.35	.250	3.17	.125	0.56	.022	0.71	.028	0.63	.025
3/8	9.50	.374	4.74	.187	0.69	.027	0.84	.033	0.76	.030
1/2	12.70	.500	6.35	.250	0.69	.027	0.84	.033	0.76	.030
3/4	19.05	.750	9.53	.375	0.76	.030	1.02	.040	0.89	.035


PRODUCT INFORMATION

1. FLAME RETARDANT
2. MATERIAL: IRRADIATED MODIFIED POLYOLEFIN
STANDARD COLOUR: BLACK
3. SHRINK RATIO 2:1
4. LONGITUDINAL CHANGE +5 TO -5%
5. TYPE 2 TUBING IS NOT FLAME RETARDED
AND AVAILABLE IN CLEAR COLOR
6. TUBING CUT TO SPECIFIC LENGTHS CAN BE SUPPLIED
FROM THE PRODUCT SIZES REFERENCED WITHIN THIS DRAWING

STANDARD CUTTING TOLERANCES (mm)	
CUT LENGTH	TOLERANCE
UPTO TO 9.90mm	±1.50mm
10mm TO 24.90mm	±1.50mm
25mm TO 54.90mm	±1.50mm
55mm TO 99.90mm	±3.00mm
100mm TO 149.90mm	±4.00mm
150mm TO 499.90mm	±5.00mm
500mm AND GREATER	±25.40mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:
 0 PLC ±.1
 1 PLC ±0.1
 2 PLC ±0.01
 3 PLC ±0.001
 4 PLC ±0.0001
 ANGLES ±
 FINISH -

DWN	10JAN2024
CHK	10JAN2024
APVD	11JAN2024
PRODUCT SPEC	108-120021
APPLICATION SPEC	114-120022
WEIGHT	-
CUSTOMER DRAWING	



TE Connectivity

NAME
CRN TUBING

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	-	CRN_TUBING	-
SCALE		SHEET	REV
NTS		1 OF 1	A