



NOTES

1. PART No. BREAKDOWN EXAMPLE:- DEUTSCH ASHD024-44420SN-025

SERIES PREFIX
SHELL STYLE
SHELL SIZE

POWER CONTACT CRIMP BUCKET SIZE
SHELL KEYING: N, A, B, C, D or E
CONTACT TYPE: P=PIN. S=SOCKET

INSERT ARRANGEMENT - 4 x SIZE 4 CONTACTS
- 4 x SIZE 20 CONTACTS

		KEY ORIENTATION				
B° ± 1°		A	B	C	D	N
		80	69	121	110	95

2. CONTACT CAVITY IDENTIFICATION, PIN CLOCKWISE, SOCKET ANTI-CLOCKWISE.

ISSUE	CHANGE NOTE	DRAWN	CHECKED	APP. ENG.	APP. MARKETING	DATE
B	57566	NDL	RBC	KJF	IKG	26/08/09
A	54386	NDL	JAK	JAK	IKG	26/06/07

MATERIAL	HEAT TREATMENT & FINISH	PACKAGING	APP. I.E.D.
----	----	----	----

© THE COPYRIGHT OF THIS DRAWING IS RESERVED BY DEUTSCH UK. IT IS ISSUED ON CONDITION THAT IT IS NOT COPIED, REPRODUCED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE CONSENT IN WRITING OF DEUTSCH UK.

GENERAL TOLERANCES UNLESS OTHERWISE STATED:
±0.4mm ON WHOLE NUMBERS
±0.2mm ON ONE PLACE DECIMALS
±0.1mm ON TWO PLACE DECIMALS
±1/2° ON ANGLES
±0.05mm ON DRILLED HOLES
ALL DIAMETERS Ø 0.10

REMOVE ALL BURRS AND SHARP EDGES 0.1 MAX. UNLESS OTHERWISE STATED.

DIMENSIONS IN MILLIMETRES UNLESS OTHERWISE STATED.

SCALE 2:1



DEUTSCH
A STEP AHEAD IN TECHNOLOGY UK

ST LEONARDS ON SEA, EAST SUSSEX, TN38 9RF
TEL. +44 (0)1424 852721

TITLE
ASHD RECEPT ASSY
44420 PLANFORM
ENVELOPE DETAILS

DRAWING NUMBER

610728-ENV