







REVISIONS				
REV	SYM	DESCRIPTION	DATE	APPROVED
NC	DRC20-75P-***	NEW RELEASE PER E.O. P20253	7-6-09	ABR



3D REAR  
SCALE 1:1




3D FRONT  
SCALE 1:1




DETAIL A  
SCALE 3:1  
FLANGE SEAL NOT SHOWN FOR CLARITY

KEY ARRANGEMENTS



- 9 RECOMMENDED SCREW: 6-19 [M3.63 X 1.34] THREAD FORMING SCREW. TORQUE: 18-20 IN-LBS [2.03-2.26 Nm].
  - 8 PIN NO. 37 ON 01 KEY SIDE IS NOT INCLUDED FOR ECM VENTING.
  - 7 THREADED INSERT MAX ALLOWABLE TORQUE 45 IN-LBS. [5.64 N-m].
  - 6 FLANGE SEAL NOT SHOWN FOR CLARITY.
  - 5. CONNECTOR MATES WITH DRC26-38S (\*\*). WHERE (\*\*)= KEY ARRANGEMENT.
  - 4. CONTACT PLATING TO BE:  
SIZE 12 - MATING SIDE: TIN; PCB SIDE: TIN  
SIZE 20 - MATING SIDE: GOLD; PCB SIDE: TIN.
  - 3. MATERIAL: SHELL -PLASTIC (BLACK), INSERT -STEEL, SEAL -RUBBER
  - 2. DIMENSION TOLERANCE ±.025 [.64]; PANEL CUTOUT: ±.010 [.25].
  - 1. DIMENSIONS ARE IN INCHES [MILLIMETERS].
- NOTES: UNLESS OTHERWISE SPECIFIED.



RECOMMENDED PANEL CUTOUT

SIGNATURE & DATE		75 PIN STRAIGHT RECEPTACLE PCB MOUNT DRC SERIES		EP	
DR	J. APOSTOL 25 JUN 2009			3850 INDUSTRIAL AVE. HEMET, CA 92545	
CHK	W. M. [Signature]			DEUTSCH	
PE	W. M. [Signature]			TIMBERLINE	
APPD	[Signature]			DRC20-75P-***	
SCALE	NONE	ENVELOPE		DWD	
				CODE 133	
				SHEET 1 OF 1	