


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	03DEC2020	RS	MF



PRODUCT SELECTION INFORMATION

TCPN	CATALOGUE NUMBER	CONDUCTOR AREA (mm ²)	STRANDING METRIC	DIMENSIONS (mm)		CRIMPING DIE
				A	G	
914602-000	CKB16	16	7/1.70	45	5.5	38-63CU
610420-000	CKB25	25	19/1.35	48	7.1	38-77CU
417270-000	CKB35	35	19/1.53	48	8.4	38-92CU
556296-000	CKB50	50	19/1.78	54	9.5	38-104CU
840278-000	CKB70	70	19/2.14	51	11	38-115CU
975512-000	CKB70	70	19/2.14	51	11	38-115CU
277742-000	CKB95	95	37/1.78	54	13.4	38-142CU
940578-000	CKB120	120	37/2.03	76	15.5	38-165CU
930690-000	CKB150	150	37/2.25	76	16.3	38-183CU
249414-000	CKB185	185	37/2.52	88	18.4	38-200CU
480162-000	CKB240	240	61/2.25	76	21.2	38-231CU
155764-000	CKB300	300	61/2.52	88	23.8	38-260CU
CN5864-000	CKB400	400	61/2.85	89	26.9	40-281CU
C47412-000	CKB630	630	127/2.52	145	33.5	40-370CU

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAVI.S 03DEC2020		
DIMENSIONS: mm		CHK S.CHAD 03DEC2020		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M.FRATER 03DEC2020	NAME COPPER CRIMP BARRIER LINKS	
<ul style="list-style-type: none"> 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±0.0001 		PRODUCT SPEC -	RESTRICTED TO -	
MATERIAL -		FINISH -	APPLICATION SPEC -	SIZE A3
		WEIGHT -	CAGE CODE 00779	DRAWING NO E00001144
CUSTOMER DRAWING			SCALE NTS	SHEET 1 OF 1
			REV A	