


REVISIONS				
P	LR	DESCRIPTION	DATE	BY
A2		INITIAL RELEASE	14MAR2023	MIN AK



All dimensions in mm [Inches]

LABEL ACROSS: 3
PER SHEET QTY: 30

TE PN: 1768017-2

1768017-2

210.00 [8.268]

250.00 [9.843]

15.00 [.591]

22.00 [.866]

21.00 [.827]

56.00 [2.205]

2.0 [0.079]

SCREEN PRINTED LINE 2mm WIDE
(1mm EITHER SIDE OF LABEL EDGE)

LABEL KISS CUT TO
CENTRE OF PRINTED LINE



SAP: 1768017-2 DESC: EB2256

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [0.02]
LABEL WIDTH:	±0.3 [0.02]
WEB WIDTH:	±0.6 [0.03]
VERTICAL REPEAT:	±0.8 [0.03]*
HORIZONTAL REPEAT:	±0.8 [0.03]*
FRONT POSITIONING:	±0.8 [0.03]*
LEFT MARGIN:	±0.4 [0.06]
QUANTITY:	-0% -2% %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PIC	±
1 PIC	±
2 PIC	±
3 PIC	±
4 PIC	±
FINISH	±
MATERIAL	-
SEE TABLE	

DMN	M. NUTTALL	14MAR2023	NAME	EB2256 - HAND WRITABLE NYLON FABRIC LABELS
CHK	M. NUTTALL	14MAR2023	PRODUCT SPEC	TTDS-181
APVD	A. KEAN	14MAR2023	APPLICATION SPEC	
WEIGHT	0.161g	SIZE	A2	QAGE CODE
CUSTOMER DRAWING		DRAWING NO	1768017-2	SCALE
		RESTRICTED TO		SHEET
				1 of 1
				REV
				A2

MATERIAL	YELLOW NYLON FABRIC
ADHESIVE TYPE	PERMANENT ACRYLIC
LINER	GLASSINE PAPER



TE Connectivity

A

B

C

D

A

B

C

D