



REVISIONS				
P	LR	DESCRIPTION	DATE	BY
A		INITIAL RELEASE	13MAR2023	YB SL

LABEL AND LINER DESIGN



PRESENTATION



QTY PER ROLL: 10,000
 LABELS ACROSS: 3
 INSIDE WOUND

TE PN: 4-1768018-6

All dimensions in mm [INCHES]

MATERIAL	SILVER POLYVINYLCHLORID
ADHESIVE TYPE	PERMANENT ACRYLIC
LINER	KRAFT WHITE

THIS DRAWING IS A CONTROLLED DOCUMENT.		NAME	
DMN	Y. BONNINO	13MAR2023	STE TE Connectivity
CHK	Y. BONNINO	13MAR2023	
APVD	S. LAZRAK	13MAR2023	EET-1325V-8A
PRODUCT SPEC			
APPLICATION SPEC			
WEIGHT	0	SIZE	A2
CUSTOMER DRAWING		QAGE CODE	A00YM
		DRAWING NO	4-1768018-6
		SCALE	NTS
		SHEET	1 of 1
		REV	1

TOLERANCES mm [INCH]	
LABEL HEIGHT:	± 0.3 [.012]
LABEL WIDTH:	± 0.3 [.012]
NER WIDTH:	± 0.07 [.003]
VERTICAL REPEAT:	± 0.8 [.031]*
HORIZONTAL REPEAT:	± 0.8 [.031]*
PRINT POSITIONING:	± 0.8 [.031]*
LEFT MARGIN:	± 0.4 [.016]
QUANTITY:	-0% +2%
*NON ACCUMULATING	

DIMENSIONS: mm [INCHES]		TOLERANCES (UNLESS OTHERWISE SPECIFIED):	
0 P/C	\pm	1 P/C	\pm
1 P/C	\pm	2 P/C	\pm
2 P/C	\pm	3 P/C	\pm
3 P/C	\pm	4 P/C	\pm
4 P/C	\pm	FINISH	\pm
MATERIAL		-	
SEE TABLE			