



LABEL AND LINER DESIGN



PRESENTATION



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	ECR-20-017666	29DEC2020	GK	MN

DESCRIPTION	TEPN	MATERIAL DESCRIPTION	TTDS	WEIGHT (g)	ROLL DIAMETER (mm) ± 10	ROLL DIAMETER (Inch) ± 0.393
EET-2551P-4	7-1768018-2	YELLOW POLYESTER	TTDS-174	0.158	149.86	5.90
EET-2551P-8A	7-1768018-3	SILVER POLYESTER	TTDS-175	0.125	149.86	5.90
EET-2551P-9	7-1768018-4	WHITE POLYESTER	TTDS-177	0.121	144.75	5.70
EET-2551PY-9	7-1768018-5	WHITE POLYETHYLENE	TTDS-178	0.143	160.95	6.34
EET-2551V-4-W	7-1768018-6	WARNING YELLOW FLEXIBLE PVC	TTDS-184	0.143	151.30	5.96
EET-2551V-8A	7-1768018-7	SILVER FLEXIBLE PVC	TTDS-PV330	0.145	149.86	5.90
EET-2551V-9	7-1768018-8	WHITE FLEXIBLE PVC	TTDS-207	0.175	153.06	6.03

INSIDE WOUND LABEL ACROSS: 1 PER ROLL QTY: 3000

ADHESIVE TYPE	PERMANENT
LINER	GLASSINE PAPER

TOLERANCES mm [INCH] LABEL HEIGHT: ±0.3 [.012] LABEL WIDTH: ±0.3 [.012] WEB WIDTH: ±0.8 [.031] VERTICAL REPEAT: ±0.8 [.031]* HORIZONTAL REPEAT: ±0.8 [.031]* PRINT POSITIONING: ±0.8 [.031]* LEFT MARGIN: ±0.4 [.016] QUANTITY: -0 % +2 % *NON ACCUMULATING	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 29DEC2020 GOPALAKRISHNA HV	TE Connectivity NAME: EET LABELS 25.40mm x 50.80mm SIZE: A3 CAGE CODE: C2290 DRAWING NO: EET-2551 RESTRICTED TO:
	DIMENSIONS: mm [INCH]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK 29DEC2020 MIKE NUTTALL	
		0 PLC ± -	APVD 29DEC2020 MIKE NUTTALL	
		1 PLC ± -	PRODUCT SPEC	
MATERIAL: SEE TABLE	2 PLC ± -	APPLICATION SPEC	WEIGHT: SEE TABLE	
	3 PLC ± -	FINISH: -	CUSTOMER DRAWING	
	4 PLC ± -		SCALE: NTS SHEET: 1 OF 1 REV: B	