



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	09DEC2016	GK	KM

PRESENTATION




PRINTING/DIMENSION



RADIUS = 4 x .060 inch [4 x 1.5 mm]

LABEL BUILD DETAIL



All dimensions in Inches [mm]

MATERIAL	THERMAL TRANSFER PRINTABLE PAPER
ADHESIVE TYPE	ACRYLIC PERMANENT
NOM THICKNESS	0.07 MM [.003 INCH]
BACKGROUND COLOURS	WHITE
WOUND	OUTSIDE WOUND

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN GOPALAKRISHNA HV 09DEC2016																																													
DIMENSIONS: INCHES[mm]		CHK K. MUNZ 09DEC2016																																													
<table border="1"> <thead> <tr> <th>TOLERANCES</th> <th>INCH[mm]</th> </tr> </thead> <tbody> <tr> <td>LABEL HEIGHT:</td> <td>±.018 [0.3]*</td> </tr> <tr> <td>LABEL WIDTH:</td> <td>±.018 [0.3]*</td> </tr> <tr> <td>WEB WIDTH:</td> <td>±.039 [1.0]*</td> </tr> <tr> <td>VERTICAL REPEAT:</td> <td>±.039 [1.0]*</td> </tr> <tr> <td>HORIZONTAL REPEAT:</td> <td>±.039 [1.0]*</td> </tr> <tr> <td>PRINT POSITIONING:</td> <td>±.039 [1.0]*</td> </tr> <tr> <td colspan="2">*NON ACCUMULATING</td> </tr> </tbody> </table>		TOLERANCES	INCH[mm]	LABEL HEIGHT:	±.018 [0.3]*	LABEL WIDTH:	±.018 [0.3]*	WEB WIDTH:	±.039 [1.0]*	VERTICAL REPEAT:	±.039 [1.0]*	HORIZONTAL REPEAT:	±.039 [1.0]*	PRINT POSITIONING:	±.039 [1.0]*	*NON ACCUMULATING		<table border="1"> <thead> <tr> <th>TOLERANCES UNLESS OTHERWISE SPECIFIED:</th> <th></th> </tr> </thead> <tbody> <tr> <td>0 PLC</td> <td>± -</td> </tr> <tr> <td>1 PLC</td> <td>± -</td> </tr> <tr> <td>2 PLC</td> <td>± -</td> </tr> <tr> <td>3 PLC</td> <td>± -</td> </tr> <tr> <td>4 PLC</td> <td>± -</td> </tr> <tr> <td>ANGLES</td> <td>± ± -</td> </tr> <tr> <td>FINISH</td> <td>-</td> </tr> </tbody> </table>		TOLERANCES UNLESS OTHERWISE SPECIFIED:		0 PLC	± -	1 PLC	± -	2 PLC	± -	3 PLC	± -	4 PLC	± -	ANGLES	± ± -	FINISH	-	<table border="1"> <tr> <td colspan="2">NAME EP ECONOMY PAPER LABEL</td> </tr> <tr> <td>SIZE</td> <td>A2</td> </tr> <tr> <td>CAGE CODE</td> <td>00779</td> </tr> <tr> <td>DRAWING NO</td> <td>EP-191064-10-9</td> </tr> <tr> <td>RESTRICTED TO</td> <td>-</td> </tr> </table>		NAME EP ECONOMY PAPER LABEL		SIZE	A2	CAGE CODE	00779	DRAWING NO	EP-191064-10-9	RESTRICTED TO	-
TOLERANCES	INCH[mm]																																														
LABEL HEIGHT:	±.018 [0.3]*																																														
LABEL WIDTH:	±.018 [0.3]*																																														
WEB WIDTH:	±.039 [1.0]*																																														
VERTICAL REPEAT:	±.039 [1.0]*																																														
HORIZONTAL REPEAT:	±.039 [1.0]*																																														
PRINT POSITIONING:	±.039 [1.0]*																																														
*NON ACCUMULATING																																															
TOLERANCES UNLESS OTHERWISE SPECIFIED:																																															
0 PLC	± -																																														
1 PLC	± -																																														
2 PLC	± -																																														
3 PLC	± -																																														
4 PLC	± -																																														
ANGLES	± ± -																																														
FINISH	-																																														
NAME EP ECONOMY PAPER LABEL																																															
SIZE	A2																																														
CAGE CODE	00779																																														
DRAWING NO	EP-191064-10-9																																														
RESTRICTED TO	-																																														
MATERIAL		CUSTOMER DRAWING		SCALE NTS																																											
		SHEET 1 OF 1		REV A1																																											