

© - TE Connectivity. All Rights Reserved.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
2		DRAWING TITLE UPDATED	24JAN2022	GSK	SM

TYPE	VOLTAGE CLASS	APPLICATION	MATERIAL NUMBER	MATERIAL NAME	TERMINATION LENGTH L (mm) [COMMENTS OSH]
COLD SHRINK TERMINATION INDOOR/OUTDOOR	12 kV	3 CORE	A31452-011	GUST-12/70-120/800-L12	800mm
			A31452-077	GUST-12/70-120/800-L12	800mm
			D06082-061	GUST-12/150-240/450	450mm
			D90123-011	GUST-12/150-240/1200	1200mm
			F96122-070	GUST-12/70-120/450-L12	450mm



THREE-CORE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SATHISH KUMAR G 24JAN2022	<b>TE</b> TE Connectivity	
DIMENSIONS: mm		CHK OSWALD HOFFMANN 24JAN2022		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD STEPHEN MORLEY 24JAN2022	NAME HEAT SHRINK TERMINATION INDOOR/OUTDOOR	
0 PLC ± -		PRODUCT SPEC	SIZE	
1 PLC ± -		APPLICATION SPEC	CAGE CODE	DRAWING NO
2 PLC ± -			A3	00779
3 PLC ± -			G-ESP-0146	
4 PLC ± -			RESTRICTED TO	
ANGLES ± -		WEIGHT	-	
MATERIAL		CUSTOMER DRAWING	SCALE	SHEET
FINISH			NTS	1 of 1
				REV 2