

REV. C
DCO 300855

TOLERANCES ±.010" - UNLESS OTHERWISE SPECIFIED

COIL: @ 25°C	
RESISTANCE _____	CURRENT: 40mA MAX.
NOMINAL VOLTAGE _____	115 VAC - 400Hz
MUST OPERATE _____	70.0 VAC MAX., 400Hz
MUST RELEASE _____	25.0 VAC MAX., 8.0 VAC MIN., 400 Hz


ENVIRONMENT:

VIBRATION	33 Hz TO 3000 Hz @ 30 g's
SHOCK	200 g's 6 MS. DURATION
TEMPERATURE	-70 °C TO +125 °C

NOTES:

OPERATE TIME	15 mS MAX.
RELEASE TIME	50 mS MAX.
CONTACT BOUNCE	1 mS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: _____

10 AMPS 28 VDC, 115 VAC 400 Hz RESISTIVE.
100,000 OPERATIONS

DR. B.D. 07MAR2008 | CK. J.M.B. 5/14/08

Tyco Electronics ©COPYRIGHT 2005
TYCO ELECTRONICS CORPORATION
ALL INTERNATIONAL RIGHTS RESERVED

CUST. _____ CATALOG ITEM _____
CUST. NO. _____ REV. _____

TE NUMBER
2-1617752-9

CII PART NUMBER
FCA-210-HX8