



REVISIONS		DATE	DWN	APVD
P	LTR	DESCRIPTION		
B		INITIAL RELEASE	200CT2020	GK MN

LABEL AND LINER DESIGN



PRESENTATION



All dimensions in mm [Inches]

TE PN: A67975-000

**OUTSIDE WOUND
LABEL ACROSS: 4
PER ROLL QTY: 10000**

TOLERANCES mm [INCH]		THIS DRAWING IS A CONTROLLED DOCUMENT.	
LABEL HEIGHT:	±0.3 [.012]	DIMENSIONS:	mm [INCHES]
LABEL WIDTH:	±0.3 [.012]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	
WEB WIDTH:	±0.8 [.031]	0 PLG	±
VERTICAL REPEAT:	±0.8 [.031]*	1 PLG	±
HORIZONTAL REPEAT:	±0.8 [.031]*	2 PLG	±
PRINT POSITIONING:	±0.8 [.031]*	3 PLG	±
LEFT MARGIN:	±0.4 [.016]	4 PLG	±
QUANTITY:	-0 % +2 %	FINISH	
*NON ACCUMULATING		-	
MATERIAL	SEE TABLE	MATERIAL	HIGH TACK WHITE POLYESTER
APVD MIKE NUTTALL 200CT2020		ADHESIVE TYPE	PERMANENT ACRYLIC
CHK GOPALAKRISHNA HV 200CT2020		LINER	GLASSINE PAPER
DWN 200CT2020		STE TE Connectivity	
NAME HW - HIGH TACK WHITE POLYESTER LABELS		RESTRICTED TO	
SIZE	A3	CAGE CODE	C2290
DRAWING NO	G=HW-203127-10-9		SCALE
SCALE	NTS	SHEET	1 OF 1
REV	B		