


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - LEB-0619P-4 ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	DRAWING FORMAT UPDATE	21DEC2018	GK	KM



LABEL ACROSS: 9
LABELS PER SHEET: 270
LABELS PER PACK: 2700
SHEETS PER PACK: 10

All dimensions in mm [INCHES]

Print Colour	Description	Material	Nom. Thickness	Adhesive Type	Part number
	LEB-0920P-8A	PE200 Silver Polyester	0.05 mm	Acrylic, permanent	6-1768033-2
	LEB-0920P-9	PE201 White Polyester	0.05 mm	Acrylic, permanent	6-1768033-3
	LEB-0920P-8	PE202 Silver-grey Polyester	0.05 mm	Acrylic, permanent	6-1768033-1
	LEB-0920P-4	PE216 Yellow Polyester	0.05 mm	Acrylic, permanent	6-1768033-0
	LEB-0920PF-4	GW201 Yellow Polyester cloth	0.10 mm	Acrylic, permanent	6-1768033-4

TOLERANCES mm [INCHES]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±

MATERIAL: SEE TABLE

FINISH: -

DWN	21DEC2018	TE Connectivity
CHK	21DEC2018	
APVD	21DEC2018	NAME
GOPALAKRISHNA HV		LEB - POLYESTER LABELS ON SHEET
K. MUNZ		SIZE
K. MUNZ		CAGE CODE
PRODUCT SPEC		DRAWING NO
APPLICATION SPEC		RESTRICTED TO
WEIGHT		0.06 g
CUSTOMER DRAWING		A2 C2290
SCALE		NTS
SHEET		1 of 1
REV		B