



P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	INITIAL RELEASE	03JUL2020	MN	AK

### LABEL AND LINER DESIGN

### PRESENTATION



All dimensions in mm [Inches]

**TE PN: F07566-000**

**OUTSIDE WOUND  
LABEL ACROSS: 5  
PER ROLL QTY: 10000**

MATERIAL	METALIZED POLYESTER
ADHESIVE TYPE	PERMANENT
LINER	GLASSINE PAPER

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
ANGLES ± -	FINISH -
MATERIAL SEE TABLE	

DWN	M. NUTTALL	03JUL2020
CHK	A. KEAN	03JUL2020
APVD	A. KEAN	03JUL2020
PRODUCT SPEC	TTDS-074	
APPLICATION SPEC	-	
WEIGHT	0.004g	
CUSTOMER DRAWING		

TE Connectivity		NAME	
		MP - METALIZED POLYESTER LABELS	
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	C2290	G-MP-089047-10-8A	-
SCALE		SHEET	REV
NTS		1 OF 1	B