

DRAWN		DATE		 3RD ANGLE PROJECTION NOT TO SCALE	PART NUMBER:		<p style="text-align: center;">60F SERIES</p>		 Polamco
P.FRYER		07/09/2011			TITLE:				
DESIGN APPROVAL		DATE		UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES GENERAL TOL LINEAR +/-0,25MM ANGULAR +/- 1°	ASSY USED ON: MIL-DTL-38999 SERIES I		 TE connectivity		
K.SHEPPARD		04/11/2010			THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.			POLAMCO LTD, WESTON LOCK, LOWER BRISTOL ROAD BATH BA2 1EP	
DOC TYPE	Customer Drawing				MATERIAL SEE PART NUMBER BREAKDOWN			SHT	
ISSUE/REV	DCR			FINISH SEE PART NUMBER BREAKDOWN		1		P17644	
NCAGE CODE U5792		WEIGHT N/A							

TABLE 1

SHELL SIZE	A THREAD	ØB MAX	ØT MIN	C ±0,5	D MAX	E MAX	F MAX	K ±0,5	J MAX	F' MAX	MAX ENTRY FOR LOW PROFILE OPTION
09	7/16-28 UNEF	18,0	6,8	16,4	26,8	22,7	26,5	15,0	18,0	27,4	04
11	9/16-24 UNEF	21,0	10,2	17,2	27,6	26,2	28,2	17,0	22,0	29,2	05
13	11/16-24 UNEF	24,5	13,1	17,6	28,0	29,2	29,7	18,0	22,0	30,7	06
15	13/16-20 UNEF	27,8	16,2	18,5	29,0	32,2	31,2	20,0	25,0	32,2	07
17	15/16-20 UNEF	30,8	19,3	19,2	29,8	35,7	32,9	21,5	27,0	33,9	08
19	1 1/16-18 UNEF	34,1	22,3	19,6	30,6	39,7	34,5	23,0	28,0	35,7	10
21	1 3/16-18 UNEF	37,3	25,8	20,4	30,9	42,2	36,1	25,0	29,0	37,1	10
23	1 5/16-18 UNEF	41,0	28,3	20,8	31,2	45,2	37,6	26,0	31,7	38,6	10
25	1 7/16-18 UNEF	43,7	31,5	21,7	32,1	48,2	39,1	28,0	31,7	40,1	10

TABLE 2

ENTRY SIZE	ØG MIN	ØH MAX	ØM MAX
04	6,3	14,3	9,5
05	7,9	15,8	11,1
06	9,5	17,4	12,7
07	11,1	19,0	14,3
08	12,7	20,6	15,9
10	15,8	23,8	19,0
12	19,0	27,0	22,2
14	22,2	30,1	25,4
16	25,4	33,3	28,6
18	28,5	36,5	31,8
20	31,7	39,7	34,9
22	34,9	42,8	38,1
24	38,1	46,0	41,3


TABLE 3

CODE	FINISH
C	ELECTROLESS NICKEL
B	CADMIUM OLIVE DRAB OVER ELECTROLESS NICKEL
ZB	ZINC COBALT OLIVE DRAB OVER ELECTROLESS NICKEL
ZN	ZINC NICKEL BLACK PASSIVATE OVER ELECTROLESS NICKEL

SEE SS0076 FOR FULL RANGE OF FINISH OPTIONS

60F1-17-08-1-C-LP-A

SERIES _____
CONNECTOR INTERFACE _____
ANGLE _____
SHELL SIZE (TABLE 1) _____
ENTRY SIZE (TABLE 2) _____
MATERIAL _____
ALUMINIUM ALLOY
FINISH (TABLE 3) _____
LOW PROFILE OPTION (90° ONLY) _____
OMIT IF STANDARD REQUIRED
RING OPTION: _____
A - RING TO SUIT SINGLE BRAID
B - RING TO SUIT DOUBLE BRAID
OMIT IF NO RING IS REQUIRED

DRAWN		DATE		 3RD ANGLE PROJECTION NOT TO SCALE	PART NUMBER:			 60F SERIES		
P.FRYER		07/09/2011			TITLE:					
DESIGN APPROVAL		DATE		<small>UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES GENERAL TOL LINEAR +/-0,25MM ANGULAR +/- 1°</small>				ASSY USED ON: MIL-DTL-38999 SERIES I		
K.SHEPPARD		04/11/2010			THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.					
DOC TYPE	Customer Drawing							MATERIAL		
ISSUE/REV		DCR		SEE PART NUMBER BREAKDOWN			2			
AA		---		FINISH			DRAWING NO:			
NCAGE CODE U5792		WEIGHT		SEE PART NUMBER BREAKDOWN			P17644			