


REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	ECR-20-003544	05MAR2020	RK	HD

Component 1 HTAT-24/6


a) Part as supplied



b) Part fully recovered



Component 2 RBK-105-NR5070/A-X



PRODUCT DIMENSIONS & NOTES

DIMENSIONS (in millimetres)

Component 1: HTAT-24/6-0			Component 2: RBK-105-NR5070/A-X				
D	d	T	H	h	L	W1	W2
MIN	MAX	NOM	±20%	±20%	±20%	±20%	±30%
a	b	b					
24.0	6.00	2.25	8.50	6.50	2.75	27.25	1.0
Supplied cut length 65mm ±3.0mm			Supplied cut length 8mm ±0.8mm				
MATERIAL: JACKET: Flame Retarded Modified Polyolefin (Colour: Black) LINER: Hot Melt Adhesive (Colour: Amber)			MATERIAL: Hot Melt Adhesive (Colour: Amber)				

TE Connectivity. All Rights Reserved.

© 2015

©

DIMENSIONS: mm	DWN	27FEB2015	MATERIAL	-	FINISH	-
	CHK	27FEB2015	TE Connectivity			
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	27FEB2015				
	CD		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
0 PLC ± -	PRODUCT SPEC	108-120026	A4	-	© RBK-105-KIT-0107-A0	-
1 PLC ± -	APPLICATION SPEC	-	WEIGHT	3.39 g	CUSTOMER DRAWING	SCALE NTS
2 PLC ± -					SHEET 1 OF 1	REV A1
3 PLC ± -						
4 PLC ± -						
ANGLES ± -						

