





P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	04SEP2019	BS	CW




NOTE:
1. TECHNICAL DATA:SEE TABLE 1
2. CONNECTION REFER TO CIRCUIT DIAGRAM;

△ RECOMMEND TORQUE 0.4NM;

注释:
1. 技术参数:参考表1
2. 连接参考电路图;

△ 推荐扭矩0.4NM;



MI2, Male, 4-pole M8, Female, 3-pole

MI2-Y2 CIRCUIT DIAGRAM
MI2-Y2 接线图

TABLE 1
TECHNICAL DATA

S4187540480-000

RATED VOLTAGE	60V
RATED CURRENT	4A
POLLUTION DEGREE	3
OVERVOLTAGE CATEGORY	II
MATERIAL GROUP	II
INSULATION RESISTANCE	≥100MΩ
DEGREE OF PROTECTION	IP65
OPERATION TEMPERATURE	-25℃~+85℃

S4187540480-000	RPC-MI2-MS-4CON-M8-Y2 MI2转M8特殊Y2型4针转接头
ASSEMBLY PART NUMBER 成品料号	ASSEMBLY PART DESCRIPTION 成品描述

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BELL SU 04SEP2019	 TE Connectivity		
DIMENSIONS: mm		CHK KEVIN HUANG 04SEP2019			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD CHRIS WANG 04SEP2019			
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC			
MATERIAL		APPLICATION SPEC	NAME RPC-MI2-MS-4CON-M8-Y2		
FINISH		WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO S4187540480000
CUSTOMER DRAWING		SCALE 3:2	SHEET 1 OF 1		REV A