



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - TE Connectivity Ltd. ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
F		NEW DRAWING	26OCT2018	GK	DB

**LABEL AND LINER DESIGN**



**PRESENTATION**



**OUTSIDE WOUND  
 LABEL ACROSS: 3  
 PER ROLL QTY: 1000**

All dimensions in mm [Inch]

**TE PN: CR4925-000**

UL-MARKING AND LABELLING SYSTEMS		
PGIS2 - Marking and Labeling Systems, Limited Use - Component (UL 969)		
File: MH61871	Product design: <b>SBP</b>	Ribbon: TMS-XXX-RIBBON-4RPSCE

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS:	mm [INCHES]
TOLERANCES UNLESS OTHERWISE SPECIFIED:	
0 PLC	±
1 PLC	±
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±
FINISH	GLOSSY
MATERIAL	SEE TABLE

MATERIAL	CLEAR VINYL		
ADHESIVE TYPE	ACRYLIC PERMANENT		
LINEAR	WHITE KRAFT		
DWN	25SEP2018		TE Connectivity
CHK	GOPALAKRISHNA HV		
APVD	D.BURGAT		
NAME	D.BURGAT		
PRODUCT SPEC	TTDS-211	SBP LABEL - YELLOW	
APPLICATION SPEC		25.4 x 150.9mm [1.00 x 5.94inch]	
WEIGHT	0.533g	SIZE	A2
CUSTOMER DRAWING		CAGE CODE	00779
		DRAWING NO	C=SBP100594YW1
		RESTRICTED TO	-
		SCALE	NTS
		SHEET	1 of 1
		REV	F